

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593288

Luminaire Tested: **HC640D010-HM63040950-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040950-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4082.6 lumens
Efficiency: N/A
Efficacy: 99.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593288

CATALOG NUMBER: HC640D010-HM63040950-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P593288

CATALOG NUMBER: HC640D010-HM63040950-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204474
5°	204297
10°	202173
15°	198106
20°	187663
25°	169467
30°	143959
35°	106287
40°	61465
45°	32631
50°	18439
55°	9644
60°	6315
65°	4488
70°	3238
75°	2436
80°	1831
85°	1824



TEST NUMBER: P593288

CATALOG NUMBER: HC640D010-HM63040950-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.8	8.6
10°-20°	976.3	23.9
20°-30°	1274.3	31.2
30°-40°	973.7	23.9
40°-50°	352.6	8.6
50°-60°	102.4	2.5
60°-70°	36.6	0.9
70°-80°	12.5	0.3
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2602.4	63.7
0°-40°	3576.1	87.6
0°-60°	4031.1	98.7
0°-90°	4082.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4082.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3730	
5°	3712	352
15°	3491	976
25°	2802	1274
35°	1588	974
45°	421	353
55°	101	102
65°	35	37
75°	12	13
85°	3	2
90°	0	



TEST NUMBER: P593288

CATALOG NUMBER: HC640D010-HM63040950-61MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3729.9
2.5°	3712.5
5°	3712.5
7.5°	3686.6
10°	3631.9
12.5°	3568.4
15°	3490.6
17.5°	3375.3
20°	3216.8
22.5°	3020.8
25°	2801.7
27.5°	2553.8
30°	2274.2
32.5°	1960.0
35°	1588.2
37.5°	1199.1
40°	858.9
42.5°	593.8
45°	420.9
47.5°	302.7
50°	216.2
52.5°	152.7
55°	100.9
57.5°	72.0
60°	57.6
62.5°	46.2
65°	34.6
67.5°	28.9
70°	20.2
72.5°	14.4
75°	11.5
77.5°	8.7
80°	5.8
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)