

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593292

Luminaire Tested: **HC640D010-HM63040950-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593292
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC640D010-HM63040950-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4543.6 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593292

CATALOG NUMBER: HC640D010-HM63040950-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P593292

CATALOG NUMBER: HC640D010-HM63040950-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	215761
5°	219122
10°	231598
15°	257873
20°	267429
25°	219418
30°	153752
35°	104895
40°	54645
45°	19211
50°	8605
55°	2753
60°	1579
65°	1129
70°	930
75°	614
80°	0
85°	0



TEST NUMBER: P593292

CATALOG NUMBER: HC640D010-HM63040950-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	385.7	8.5
10°-20°	1277.9	28.1
20°-30°	1627.1	35.8
30°-40°	969.7	21.3
40°-50°	235.2	5.2
50°-60°	36.1	0.8
60°-70°	8.9	0.2
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3290.7	72.4
0°-40°	4260.4	93.8
0°-60°	4531.7	99.7
0°-90°	4543.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4543.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3936	
5°	3982	386
15°	4544	1278
25°	3628	1627
35°	1567	970
45°	248	235
55°	29	36
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P593292

CATALOG NUMBER: HC640D010-HM63040950-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	3935.8
2.5°	3935.8
5°	3981.9
7.5°	4053.9
10°	4160.5
12.5°	4327.6
15°	4543.7
17.5°	4679.2
20°	4584.1
22.5°	4218.2
25°	3627.5
27.5°	2976.3
30°	2428.9
32.5°	1985.2
35°	1567.4
37.5°	1155.4
40°	763.6
42.5°	412.1
45°	247.8
47.5°	155.6
50°	100.9
52.5°	60.5
55°	28.8
57.5°	17.3
60°	14.4
62.5°	11.5
65°	8.7
67.5°	5.8
70°	5.8
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)