

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593434

Luminaire Tested: **HC660D010-HM64560950-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560950-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5407.3 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593434

CATALOG NUMBER: HC660D010-HM64560950-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P593434

CATALOG NUMBER: HC660D010-HM64560950-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	211770
5°	213174
10°	215638
15°	220064
20°	221301
25°	214410
30°	194511
35°	158153
40°	104975
45°	58425
50°	32749
55°	18179
60°	10032
65°	7601
70°	5273
75°	3876
80°	2305
85°	2327



TEST NUMBER: P593434

CATALOG NUMBER: HC660D010-HM64560950-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	369.7	6.8
10°-20°	1093.3	20.2
20°-30°	1611.5	29.8
30°-40°	1441.4	26.7
40°-50°	625.3	11.6
50°-60°	183.7	3.4
60°-70°	58.7	1.1
70°-80°	20.7	0.4
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3074.5	56.9
0°-40°	4515.9	83.5
0°-60°	5324.9	98.5
0°-90°	5407.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5407.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3863	
5°	3874	370
15°	3878	1093
25°	3545	1611
35°	2363	1441
45°	754	625
55°	190	184
65°	59	59
75°	18	21
85°	4	3
90°	0	



TEST NUMBER: P593434

CATALOG NUMBER: HC660D010-HM64560950-61WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3863.0
2.5°	3852.0
5°	3873.8
7.5°	3881.2
10°	3873.8
12.5°	3873.8
15°	3877.5
17.5°	3855.7
20°	3793.4
22.5°	3687.3
25°	3544.7
27.5°	3343.5
30°	3072.8
32.5°	2750.9
35°	2363.2
37.5°	1920.5
40°	1466.9
42.5°	1071.8
45°	753.6
47.5°	537.8
50°	384.0
52.5°	274.4
55°	190.2
57.5°	128.0
60°	91.5
62.5°	73.2
65°	58.6
67.5°	43.9
70°	32.9
72.5°	25.6
75°	18.3
77.5°	14.6
80°	7.3
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)