

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593435

Luminaire Tested: **HC6R60D010-HM64560950-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593435
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R60D010-HM64560950-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5761.9 lumens
Efficiency: N/A
Efficacy: 104.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593435

CATALOG NUMBER: HC6R60D010-HM64560950-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P593435

CATALOG NUMBER: HC6R60D010-HM64560950-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267259
5°	273106
10°	289501
15°	323594
20°	338812
25°	282494
30°	197708
35°	133143
40°	68571
45°	23816
50°	10601
55°	3498
60°	1601
65°	1427
70°	1170
75°	784
80°	1168
85°	0



TEST NUMBER: P593435

CATALOG NUMBER: HC6R60D010-HM64560950-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	481.0	8.3
10°-20°	1606.5	27.9
20°-30°	2087.8	36.2
30°-40°	1233.3	21.4
40°-50°	294.2	5.1
50°-60°	43.4	0.8
60°-70°	10.8	0.2
70°-80°	4.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4175.4	72.5
0°-40°	5408.6	93.9
0°-60°	5746.2	99.7
0°-90°	5761.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5761.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4875	
5°	4963	481
15°	5702	1606
25°	4670	2088
35°	1990	1233
45°	307	294
55°	37	43
65°	11	11
75°	4	4
85°	0	1
90°	0	



TEST NUMBER: P593435

CATALOG NUMBER: HC6R60D010-HM64560950-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4875.2
2.5°	4886.1
5°	4962.9
7.5°	5061.7
10°	5200.7
12.5°	5420.0
15°	5701.7
17.5°	5891.9
20°	5807.7
22.5°	5383.5
25°	4670.3
27.5°	3854.8
30°	3123.3
32.5°	2527.2
35°	1989.5
37.5°	1462.9
40°	958.2
42.5°	523.0
45°	307.2
47.5°	190.2
50°	124.3
52.5°	73.2
55°	36.6
57.5°	18.3
60°	14.6
62.5°	14.6
65°	11.0
67.5°	7.3
70°	7.3
72.5°	3.7
75°	3.7
77.5°	3.7
80°	3.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)