

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593440

Luminaire Tested: **HC660D010-HM64560950-61NDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560950-61NDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4975.9 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593440

CATALOG NUMBER: HC660D010-HM64560950-61NDW

Luminous Intensity Polar Plot





TEST NUMBER: P593440

CATALOG NUMBER: HC660D010-HM64560950-61NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188466
5°	187574
10°	183430
15°	179127
20°	172390
25°	163038
30°	148168
35°	119926
40°	80873
45°	55579
50°	45542
55°	39855
60°	37694
65°	35581
70°	33419
75°	31750
80°	28855
85°	25348



TEST NUMBER: P593440

CATALOG NUMBER: HC660D010-HM64560950-61NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.8	6.5
10°-20°	886.3	17.8
20°-30°	1231.4	24.7
30°-40°	1096.4	22.0
40°-50°	582.0	11.7
50°-60°	380.6	7.6
60°-70°	272.8	5.5
70°-80°	158.2	3.2
80°-90°	46.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2439.5	49.0
0°-40°	3535.9	71.1
0°-60°	4498.6	90.4
0°-90°	4975.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4975.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3438	
5°	3409	322
15°	3156	886
25°	2695	1231
35°	1792	1096
45°	717	582
55°	417	381
65°	274	273
75°	150	158
85°	40	46
90°	0	



TEST NUMBER: P593440

CATALOG NUMBER: HC660D010-HM64560950-61NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3437.9
2.5°	3419.6
5°	3408.6
7.5°	3368.4
10°	3295.2
12.5°	3229.4
15°	3156.2
17.5°	3064.8
20°	2955.0
22.5°	2830.7
25°	2695.4
27.5°	2538.2
30°	2340.7
32.5°	2102.9
35°	1792.0
37.5°	1448.2
40°	1130.1
42.5°	877.8
45°	716.9
47.5°	610.7
50°	534.0
52.5°	471.8
55°	417.0
57.5°	376.7
60°	343.8
62.5°	310.9
65°	274.3
67.5°	241.4
70°	208.5
72.5°	179.2
75°	149.9
77.5°	120.7
80°	91.4
82.5°	65.9
85°	40.3
87.5°	18.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)