

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582564

Luminaire Tested: **HC645D010-HM64560827-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582564  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC645D010-HM64560827-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4152.6 lumens  
Efficiency: N/A  
Efficacy: 94.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582564

CATALOG NUMBER: HC645D010-HM64560827-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582564

CATALOG NUMBER: HC645D010-HM64560827-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	157279
5°	156537
10°	153081
15°	149496
20°	143874
25°	136066
30°	123652
35°	100090
40°	67491
45°	46377
50°	38003
55°	33251
60°	31456
65°	29705
70°	27889
75°	26518
80°	24119
85°	21071



TEST NUMBER: P582564

CATALOG NUMBER: HC645D010-HM64560827-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	268.5	6.5
10°-20°	739.7	17.8
20°-30°	1027.7	24.7
30°-40°	915.0	22.0
40°-50°	485.7	11.7
50°-60°	317.7	7.6
60°-70°	227.7	5.5
70°-80°	132.1	3.2
80°-90°	38.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2035.9	49.0
0°-40°	2950.9	71.1
0°-60°	3754.3	90.4
0°-90°	4152.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4152.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2869	
5°	2845	269
15°	2634	740
25°	2250	1028
35°	1496	915
45°	598	486
55°	348	318
65°	229	228
75°	125	132
85°	34	39
90°	0	



TEST NUMBER: P582564

CATALOG NUMBER: HC645D010-HM64560827-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2869.0
2.5°	2853.8
5°	2844.6
7.5°	2811.1
10°	2750.0
12.5°	2695.1
15°	2634.1
17.5°	2557.7
20°	2466.2
22.5°	2362.4
25°	2249.5
27.5°	2118.2
30°	1953.4
32.5°	1755.0
35°	1495.6
37.5°	1208.7
40°	943.1
42.5°	732.5
45°	598.2
47.5°	509.7
50°	445.6
52.5°	393.8
55°	347.9
57.5°	314.4
60°	286.9
62.5°	259.5
65°	229.0
67.5°	201.4
70°	174.0
72.5°	149.6
75°	125.2
77.5°	100.8
80°	76.4
82.5°	54.9
85°	33.5
87.5°	15.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)