

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593442

Luminaire Tested: **HC660D010-HM64560950-61WDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P593442  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC660D010-HM64560950-61WDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5337.8 lumens  
Efficiency: N/A  
Efficacy: 97.1 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 55  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P593442

CATALOG NUMBER: HC660D010-HM64560950-61WDW

### Luminous Intensity Polar Plot





TEST NUMBER: P593442

CATALOG NUMBER: HC660D010-HM64560950-61WDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	182151
5°	182038
10°	180279
15°	178412
20°	173370
25°	166050
30°	154106
35°	132588
40°	96781
45°	66317
50°	53303
55°	46469
60°	42880
65°	40783
70°	38067
75°	35605
80°	32327
85°	27613



TEST NUMBER: P593442

CATALOG NUMBER: HC660D010-HM64560950-61WDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	313.6	5.9
10°-20°	882.9	16.5
20°-30°	1255.6	23.5
30°-40°	1208.9	22.6
40°-50°	695.5	13.0
50°-60°	440.7	8.3
60°-70°	312.0	5.8
70°-80°	177.9	3.3
80°-90°	50.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2452.1	45.9
0°-40°	3661.0	68.6
0°-60°	4797.2	89.9
0°-90°	5337.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5337.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3323	
5°	3308	314
15°	3144	883
25°	2745	1256
35°	1981	1209
45°	855	696
55°	486	441
65°	314	312
75°	168	178
85°	44	51
90°	0	



TEST NUMBER: P593442

CATALOG NUMBER: HC660D010-HM64560950-61WDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3322.7
2.5°	3308.0
5°	3308.0
7.5°	3286.2
10°	3238.6
12.5°	3191.1
15°	3143.6
17.5°	3070.5
20°	2971.8
22.5°	2862.1
25°	2745.2
27.5°	2602.6
30°	2434.5
32.5°	2229.8
35°	1981.2
37.5°	1677.8
40°	1352.4
42.5°	1067.4
45°	855.4
47.5°	720.1
50°	625.0
52.5°	548.3
55°	486.2
57.5°	431.3
60°	391.1
62.5°	354.5
65°	314.4
67.5°	277.8
70°	237.5
72.5°	201.1
75°	168.1
77.5°	135.3
80°	102.4
82.5°	73.1
85°	43.9
87.5°	18.3
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)