

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582577

Luminaire Tested: **HC645D010-HM64560830-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC645D010-HM64560830-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5196.2 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582577

CATALOG NUMBER: HC645D010-HM64560830-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582577

CATALOG NUMBER: HC645D010-HM64560830-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246757
5°	250599
10°	264869
15°	294922
20°	305845
25°	250932
30°	175837
35°	119966
40°	62489
45°	21971
50°	9833
55°	3154
60°	1798
65°	1284
70°	1058
75°	699
80°	0
85°	0



TEST NUMBER: P582577

CATALOG NUMBER: HC645D010-HM64560830-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	441.1	8.5
10°-20°	1461.4	28.1
20°-30°	1860.8	35.8
30°-40°	1109.0	21.3
40°-50°	268.9	5.2
50°-60°	41.3	0.8
60°-70°	10.1	0.2
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3763.4	72.4
0°-40°	4872.4	93.8
0°-60°	5182.6	99.7
0°-90°	5196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4501	
5°	4554	441
15°	5196	1461
25°	4148	1861
35°	1793	1109
45°	283	269
55°	33	41
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582577

CATALOG NUMBER: HC645D010-HM64560830-61MDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	4501.2
2.5°	4501.2
5°	4553.9
7.5°	4636.3
10°	4758.2
12.5°	4949.4
15°	5196.5
17.5°	5351.3
20°	5242.6
22.5°	4824.1
25°	4148.5
27.5°	3403.9
30°	2777.8
32.5°	2270.3
35°	1792.6
37.5°	1321.4
40°	873.2
42.5°	471.2
45°	283.4
47.5°	177.9
50°	115.3
52.5°	69.2
55°	33.0
57.5°	19.8
60°	16.4
62.5°	13.1
65°	9.9
67.5°	6.6
70°	6.6
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)