

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582580

Luminaire Tested: **HC645D010-HM64560830-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC645D010-HM64560830-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5018.3 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582580

CATALOG NUMBER: HC645D010-HM64560830-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582580

CATALOG NUMBER: HC645D010-HM64560830-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299696
5°	300296
10°	305238
15°	307465
20°	281057
25°	220851
30°	161664
35°	114673
40°	54237
45°	20700
50°	9270
55°	2523
60°	1085
65°	856
70°	529
75°	699
80°	0
85°	0



TEST NUMBER: P582580

CATALOG NUMBER: HC645D010-HM64560830-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	522.0	10.4
10°-20°	1497.3	29.8
20°-30°	1665.5	33.2
30°-40°	1040.4	20.7
40°-50°	247.2	4.9
50°-60°	35.3	0.7
60°-70°	7.3	0.1
70°-80°	3.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3684.9	73.4
0°-40°	4725.3	94.2
0°-60°	5007.9	99.8
0°-90°	5018.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5018.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5467	
5°	5457	522
15°	5418	1497
25°	3651	1666
35°	1714	1040
45°	267	247
55°	26	35
65°	7	7
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582580

CATALOG NUMBER: HC645D010-HM64560830-61NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5466.9
2.5°	5443.8
5°	5457.0
7.5°	5476.7
10°	5483.4
12.5°	5480.0
15°	5417.5
17.5°	5206.6
20°	4817.7
22.5°	4270.7
25°	3651.2
27.5°	3058.0
30°	2553.9
32.5°	2135.3
35°	1713.5
37.5°	1258.7
40°	757.9
42.5°	438.2
45°	267.0
47.5°	171.4
50°	108.7
52.5°	62.6
55°	26.4
57.5°	13.1
60°	9.9
62.5°	9.9
65°	6.6
67.5°	6.6
70°	3.3
72.5°	3.3
75°	3.3
77.5°	3.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)