

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583320

Luminaire Tested: **HC607D010-HM60525835-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583320  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC607D010-HM60525835-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 873.9 lumens  
Efficiency: N/A  
Efficacy: 109.2 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583320

CATALOG NUMBER: HC607D010-HM60525835-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P583320

CATALOG NUMBER: HC607D010-HM60525835-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	33100
5°	32941
10°	32214
15°	31459
20°	30272
25°	28635
30°	26023
35°	21061
40°	14205
45°	9761
50°	8000
55°	6996
60°	6622
65°	6252
70°	5866
75°	5571
80°	5083
85°	4403



TEST NUMBER: P583320

CATALOG NUMBER: HC607D010-HM60525835-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.5	6.5
10°-20°	155.7	17.8
20°-30°	216.3	24.7
30°-40°	192.6	22.0
40°-50°	102.2	11.7
50°-60°	66.8	7.6
60°-70°	47.9	5.5
70°-80°	27.8	3.2
80°-90°	8.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	428.4	49.0
0°-40°	621.0	71.1
0°-60°	790.1	90.4
0°-90°	873.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	873.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	604	
5°	599	57
15°	554	156
25°	473	216
35°	315	193
45°	126	102
55°	73	67
65°	48	48
75°	26	28
85°	7	8
90°	0	



TEST NUMBER: P583320

CATALOG NUMBER: HC607D010-HM60525835-61NDW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	603.8
2.5°	600.5
5°	598.6
7.5°	591.5
10°	578.7
12.5°	567.2
15°	554.3
17.5°	538.3
20°	518.9
22.5°	497.2
25°	473.4
27.5°	445.7
30°	411.1
32.5°	369.4
35°	314.7
37.5°	254.4
40°	198.5
42.5°	154.2
45°	125.9
47.5°	107.3
50°	93.8
52.5°	82.8
55°	73.2
57.5°	66.2
60°	60.4
62.5°	54.6
65°	48.2
67.5°	42.4
70°	36.6
72.5°	31.5
75°	26.3
77.5°	21.2
80°	16.1
82.5°	11.6
85°	7.0
87.5°	3.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)