

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582587

Luminaire Tested: **HC645D010-HM64560830-61WDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582587  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC645D010-HM64560830-61WDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5314.8 lumens  
Efficiency: N/A  
Efficacy: 120.8 lumens/watt  
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 44  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582587

CATALOG NUMBER: HC645D010-HM64560830-61WDC

### Luminous Intensity Polar Plot





TEST NUMBER: P582587

CATALOG NUMBER: HC645D010-HM64560830-61WDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	82	88	84	81	85	82	80	78	78	78	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61	61	61	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56	56	56	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52	52	52	52
9	71	61	55	50	70	60	54	50	60	54	50	59	53	50	58	53	50	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	46	55	50	46	54	50	46	45	45	45	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	188422
5°	190958
10°	198115
15°	215455
20°	240885
25°	253545
30°	223199
35°	154820
40°	92445
45°	43943
50°	16588
55°	6929
60°	2171
65°	1699
70°	1058
75°	699
80°	1042
85°	0



TEST NUMBER: P582587

CATALOG NUMBER: HC645D010-HM64560830-61WDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	334.0	6.3
10°-20°	1090.1	20.5
20°-30°	1867.9	35.1
30°-40°	1450.7	27.3
40°-50°	479.6	9.0
50°-60°	73.5	1.4
60°-70°	13.0	0.2
70°-80°	4.8	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3291.9	61.9
0°-40°	4742.6	89.2
0°-60°	5295.7	99.6
0°-90°	5314.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5314.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3437	
5°	3470	334
15°	3796	1090
25°	4192	1868
35°	2313	1451
45°	567	480
55°	72	74
65°	13	13
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582587

CATALOG NUMBER: HC645D010-HM64560830-61WDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3437.1
2.5°	3433.8
5°	3470.1
7.5°	3509.6
10°	3559.0
12.5°	3657.9
15°	3796.3
17.5°	3964.4
20°	4129.1
22.5°	4224.7
25°	4191.7
27.5°	3964.4
30°	3526.0
32.5°	2936.3
35°	2313.4
37.5°	1756.5
40°	1291.8
42.5°	912.8
45°	566.8
47.5°	316.4
50°	194.5
52.5°	118.6
55°	72.5
57.5°	36.2
60°	19.8
62.5°	16.4
65°	13.1
67.5°	9.9
70°	6.6
72.5°	6.6
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)