

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593040

Luminaire Tested: **HC607D010-HM60525950-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593040
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525950-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 910.5 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593040

CATALOG NUMBER: HC607D010-HM60525950-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P593040

CATALOG NUMBER: HC607D010-HM60525950-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 94 | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 101 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 92 | 90 | 89 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 95 | 90 | 86 | 92 | 88 | 85 | 90 | 86 | 84 | 87 | 85 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 89 | 83 | 80 | 86 | 82 | 79 | 84 | 81 | 78 | 83 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 73 | 81 | 76 | 73 | 80 | 75 | 72 | 78 | 74 | 72 | 70 | | | |
| 6 | 88 | 79 | 73 | 68 | 86 | 78 | 72 | 68 | 76 | 71 | 68 | 75 | 71 | 67 | 74 | 70 | 67 | 65 | | | |
| 7 | 83 | 74 | 68 | 64 | 82 | 73 | 68 | 63 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 62 | 61 | | | |
| 8 | 79 | 70 | 63 | 59 | 78 | 69 | 63 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | |
| 9 | 75 | 66 | 60 | 56 | 74 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 54 | | | |
| 10 | 72 | 62 | 56 | 52 | 71 | 61 | 56 | 52 | 61 | 55 | 52 | 60 | 55 | 52 | 59 | 55 | 52 | 50 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 43242 |
| 5° | 43914 |
| 10° | 46414 |
| 15° | 51680 |
| 20° | 53590 |
| 25° | 43968 |
| 30° | 30809 |
| 35° | 21021 |
| 40° | 10956 |
| 45° | 3845 |
| 50° | 1723 |
| 55° | 554 |
| 60° | 307 |
| 65° | 221 |
| 70° | 176 |
| 75° | 127 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P593040

CATALOG NUMBER: HC607D010-HM60525950-61MDC

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 77.3 | 8.5 |
| 10°-20° | 256.1 | 28.1 |
| 20°-30° | 326.1 | 35.8 |
| 30°-40° | 194.3 | 21.3 |
| 40°-50° | 47.1 | 5.2 |
| 50°-60° | 7.2 | 0.8 |
| 60°-70° | 1.7 | 0.2 |
| 70°-80° | 0.6 | 0.1 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 659.5 | 72.4 |
| 0°-40° | 853.8 | 93.8 |
| 0°-60° | 908.2 | 99.7 |
| 0°-90° | 910.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 910.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 789 | |
| 5° | 798 | 77 |
| 15° | 911 | 256 |
| 25° | 727 | 326 |
| 35° | 314 | 194 |
| 45° | 50 | 47 |
| 55° | 6 | 7 |
| 65° | 2 | 2 |
| 75° | 1 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P593040

CATALOG NUMBER: HC607D010-HM60525950-61MDC

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 788.8 |
| 2.5° | 788.8 |
| 5° | 798.0 |
| 7.5° | 812.5 |
| 10° | 833.8 |
| 12.5° | 867.3 |
| 15° | 910.6 |
| 17.5° | 937.8 |
| 20° | 918.6 |
| 22.5° | 845.3 |
| 25° | 726.9 |
| 27.5° | 596.5 |
| 30° | 486.7 |
| 32.5° | 397.8 |
| 35° | 314.1 |
| 37.5° | 231.6 |
| 40° | 153.1 |
| 42.5° | 82.6 |
| 45° | 49.6 |
| 47.5° | 31.2 |
| 50° | 20.2 |
| 52.5° | 12.1 |
| 55° | 5.8 |
| 57.5° | 3.5 |
| 60° | 2.8 |
| 62.5° | 2.3 |
| 65° | 1.7 |
| 67.5° | 1.1 |
| 70° | 1.1 |
| 72.5° | 0.6 |
| 75° | 0.6 |
| 77.5° | 0.6 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)