

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582671

Luminaire Tested: **HC645D010-HM64560935-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC645D010-HM64560935-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4452.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582671

CATALOG NUMBER: HC645D010-HM64560935-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582671

CATALOG NUMBER: HC645D010-HM64560935-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	66	62	61		
8	79	70	64	59	78	69	63	59	68	63	59	67	62	59	66	62	59	57		
9	75	66	60	56	74	65	59	56	64	59	55	63	59	55	62	58	55	54		
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272571
5°	271417
10°	264997
15°	251551
20°	224212
25°	188872
30°	150479
35°	107358
40°	57730
45°	24739
50°	11241
55°	4100
60°	2017
65°	1596
70°	1459
75°	635
80°	947
85°	0



TEST NUMBER: P582671

CATALOG NUMBER: HC645D010-HM64560935-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	465.6	10.5
10°-20°	1228.6	27.6
20°-30°	1423.0	32.0
30°-40°	983.9	22.1
40°-50°	284.1	6.4
50°-60°	48.9	1.1
60°-70°	12.5	0.3
70°-80°	4.8	0.1
80°-90°	1.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3117.2	70.0
0°-40°	4101.1	92.1
0°-60°	4434.1	99.6
0°-90°	4452.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4452.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4972	
5°	4932	466
15°	4432	1229
25°	3122	1423
35°	1604	984
45°	319	284
55°	43	49
65°	12	12
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582671

CATALOG NUMBER: HC645D010-HM64560935-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4972.1
2.5°	4950.6
5°	4932.2
7.5°	4877.1
10°	4760.5
12.5°	4619.4
15°	4432.3
17.5°	4168.5
20°	3843.3
22.5°	3484.5
25°	3122.5
27.5°	2751.4
30°	2377.2
32.5°	2003.0
35°	1604.2
37.5°	1190.1
40°	806.7
42.5°	509.2
45°	319.1
47.5°	205.5
50°	131.8
52.5°	79.8
55°	42.9
57.5°	24.5
60°	18.4
62.5°	15.4
65°	12.3
67.5°	9.1
70°	9.1
72.5°	6.1
75°	3.0
77.5°	3.0
80°	3.0
82.5°	3.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)