

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583725

Luminaire Tested: **HC810D010-HM80520830-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520830-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1275.7 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583725

CATALOG NUMBER: HC810D010-HM80520830-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583725

CATALOG NUMBER: HC810D010-HM80520830-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10		0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22403
5°	22250
10°	22191
15°	22775
20°	24657
25°	26433
30°	25843
35°	21521
40°	13219
45°	9154
50°	6985
55°	4580
60°	2868
65°	2145
70°	2164
75°	2490
80°	2752
85°	2477



TEST NUMBER: P583725

CATALOG NUMBER: HC810D010-HM80520830-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.3	5.4
10°-20°	204.8	16.1
20°-30°	352.5	27.6
30°-40°	341.6	26.8
40°-50°	168.2	13.2
50°-60°	79.4	6.2
60°-70°	31.3	2.5
70°-80°	21.6	1.7
80°-90°	8.0	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.6	49.0
0°-40°	967.2	75.8
0°-60°	1214.8	95.2
0°-90°	1275.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1275.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	726	
5°	719	68
15°	713	205
25°	777	353
35°	572	342
45°	210	168
55°	85	79
65°	29	31
75°	21	22
85°	7	8
90°	0	



TEST NUMBER: P583725

CATALOG NUMBER: HC810D010-HM80520830-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	726.5
2.5°	724.2
5°	718.8
7.5°	713.4
10°	708.7
12.5°	708.0
15°	713.4
17.5°	729.6
20°	751.4
22.5°	770.7
25°	776.9
27.5°	762.9
30°	725.8
32.5°	664.6
35°	571.7
37.5°	443.8
40°	328.4
42.5°	254.8
45°	209.9
47.5°	176.6
50°	145.6
52.5°	114.7
55°	85.2
57.5°	62.0
60°	46.5
62.5°	36.4
65°	29.4
67.5°	25.6
70°	24.0
72.5°	22.5
75°	20.9
77.5°	18.6
80°	15.5
82.5°	11.7
85°	7.0
87.5°	3.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)