

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582742

Luminaire Tested: **HC650D010-HM64560835-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560835-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5549.3 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582742

CATALOG NUMBER: HC650D010-HM64560835-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P582742

CATALOG NUMBER: HC650D010-HM64560835-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			94
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			82
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			76
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			71
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			67
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			62
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	331404
5°	332065
10°	337530
15°	339991
20°	310798
25°	244218
30°	178762
35°	126806
40°	59984
45°	22878
50°	10251
55°	2791
60°	1206
65°	947
70°	593
75°	784
80°	0
85°	0



TEST NUMBER: P582742

CATALOG NUMBER: HC650D010-HM64560835-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	577.3	10.4
10°-20°	1655.8	29.8
20°-30°	1841.7	33.2
30°-40°	1150.5	20.7
40°-50°	273.3	4.9
50°-60°	39.1	0.7
60°-70°	8.1	0.1
70°-80°	3.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4074.8	73.4
0°-40°	5225.3	94.2
0°-60°	5537.7	99.8
0°-90°	5549.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5549.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6045	
5°	6034	577
15°	5991	1656
25°	4038	1842
35°	1895	1151
45°	295	273
55°	29	39
65°	7	8
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P582742

CATALOG NUMBER: HC650D010-HM64560835-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	6045.3
2.5°	6019.8
5°	6034.3
7.5°	6056.3
10°	6063.5
12.5°	6059.8
15°	5990.6
17.5°	5757.4
20°	5327.5
22.5°	4722.6
25°	4037.5
27.5°	3381.6
30°	2824.0
32.5°	2361.3
35°	1894.8
37.5°	1392.0
40°	838.2
42.5°	484.7
45°	295.1
47.5°	189.4
50°	120.2
52.5°	69.2
55°	29.2
57.5°	14.5
60°	11.0
62.5°	11.0
65°	7.3
67.5°	7.3
70°	3.7
72.5°	3.7
75°	3.7
77.5°	3.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)