

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583716

Luminaire Tested: **HC810D010-HM80520830-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520830-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1048.6 lumens
Efficiency: N/A
Efficacy: 105.9 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583716

CATALOG NUMBER: HC810D010-HM80520830-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P583716

CATALOG NUMBER: HC810D010-HM80520830-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	88	84	90	86	83	88	85	82	86	83	81	80	80	80	80
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75	75	75	75
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72	72	72	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68	68	68	68
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65	65	65	65
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83449
5°	70696
10°	51295
15°	38520
20°	30390
25°	24518
30°	18167
35°	7363
40°	3108
45°	1666
50°	748
55°	376
60°	234
65°	168
70°	144
75°	83
80°	124
85°	248



TEST NUMBER: P583716

CATALOG NUMBER: HC810D010-HM80520830-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.1	18.7
10°-20°	338.9	32.3
20°-30°	327.7	31.2
30°-40°	143.9	13.7
40°-50°	31.1	3.0
50°-60°	7.0	0.7
60°-70°	2.4	0.2
70°-80°	0.9	0.1
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.6	82.3
0°-40°	1006.6	96.0
0°-60°	1044.7	99.6
0°-90°	1048.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1048.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2706	
5°	2284	196
15°	1207	339
25°	721	328
35°	196	144
45°	38	31
55°	7	7
65°	2	2
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P583716

CATALOG NUMBER: HC810D010-HM80520830-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2706.2
1°	2685.9
2°	2630.6
3°	2530.8
4°	2411.7
5°	2283.9
6°	2144.5
7°	2004.3
8°	1872.6
9°	1750.4
10°	1638.2
11°	1532.2
12°	1437.2
13°	1350.7
14°	1274.4
15°	1206.6
17.5°	1054.8
20°	926.1
22.5°	813.3
25°	720.6
27.5°	626.2
30°	510.2
32.5°	346.7
35°	195.6
37.5°	115.3
40°	77.2
42.5°	54.6
45°	38.2
47.5°	24.9
50°	15.6
52.5°	9.4
55°	7.0
57.5°	5.4
60°	3.8
62.5°	3.1
65°	2.3
67.5°	1.6
70°	1.6
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.7



TEST NUMBER: P583716

CATALOG NUMBER: HC810D010-HM80520830-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°		0.7
87.5°		0.7



(END OF REPORT)