

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582741

Luminaire Tested: **HC650D010-HM64560835-61MDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582741  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC650D010-HM64560835-61MDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5031.8 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582741

CATALOG NUMBER: HC650D010-HM64560835-61MDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582741

CATALOG NUMBER: HC650D010-HM64560835-61MDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 111 | 108 | 104 | 101 | 109 | 105 | 102 | 100 | 101 | 99  | 96  | 97  | 95  | 94  | 94  | 92  | 91  | 89  |    |    | 89  |
| 2   | 104 | 97  | 92  | 87  | 101 | 95  | 90  | 86  | 92  | 88  | 84  | 89  | 85  | 82  | 86  | 83  | 81  | 79  |    |    | 79  |
| 3   | 97  | 88  | 82  | 76  | 94  | 87  | 81  | 76  | 84  | 79  | 75  | 81  | 77  | 73  | 79  | 75  | 72  | 70  |    |    | 70  |
| 4   | 90  | 80  | 73  | 68  | 88  | 79  | 73  | 67  | 77  | 71  | 67  | 75  | 70  | 66  | 73  | 68  | 65  | 63  |    |    | 63  |
| 5   | 84  | 74  | 66  | 61  | 82  | 73  | 66  | 61  | 71  | 65  | 60  | 69  | 64  | 59  | 67  | 63  | 59  | 57  |    |    | 57  |
| 6   | 79  | 68  | 61  | 55  | 77  | 67  | 60  | 55  | 65  | 59  | 55  | 64  | 58  | 54  | 62  | 58  | 54  | 52  |    |    | 52  |
| 7   | 74  | 63  | 55  | 50  | 73  | 62  | 55  | 50  | 61  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 49  | 48  |    |    | 48  |
| 8   | 70  | 58  | 51  | 46  | 69  | 58  | 51  | 46  | 57  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 45  | 44  |    |    | 44  |
| 9   | 66  | 54  | 47  | 43  | 65  | 54  | 47  | 42  | 53  | 47  | 42  | 52  | 46  | 42  | 51  | 46  | 42  | 40  |    |    | 40  |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 44  | 39  | 49  | 43  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 37  |    |    | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 187315 |
| 5°  | 186627 |
| 10° | 183508 |
| 15° | 180279 |
| 20° | 174047 |
| 25° | 165040 |
| 30° | 150112 |
| 35° | 119946 |
| 40° | 80029  |
| 45° | 57052  |
| 50° | 47529  |
| 55° | 41432  |
| 60° | 39142  |
| 65° | 36852  |
| 70° | 33868  |
| 75° | 31644  |
| 80° | 28760  |
| 85° | 25160  |



TEST NUMBER: P582741

CATALOG NUMBER: HC650D010-HM64560835-61MDW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 320.7  | 6.4       |
| 10°-20°   | 891.9  | 17.7      |
| 20°-30°   | 1246.3 | 24.8      |
| 30°-40°   | 1097.9 | 21.8      |
| 40°-50°   | 593.1  | 11.8      |
| 50°-60°   | 396.6  | 7.9       |
| 60°-70°   | 281.1  | 5.6       |
| 70°-80°   | 158.0  | 3.1       |
| 80°-90°   | 46.0   | 0.9       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2459.0 | 48.9      |
| 0°-40°    | 3556.9 | 70.7      |
| 0°-60°    | 4546.6 | 90.4      |
| 0°-90°    | 5031.8 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5031.8 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3417 |      |
| 5°  | 3391 | 321  |
| 15° | 3176 | 892  |
| 25° | 2728 | 1246 |
| 35° | 1792 | 1098 |
| 45° | 736  | 593  |
| 55° | 434  | 397  |
| 65° | 284  | 281  |
| 75° | 149  | 158  |
| 85° | 40   | 46   |
| 90° | 0    |      |



TEST NUMBER: P582741

CATALOG NUMBER: HC650D010-HM64560835-61MDW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3416.9 |
| 2.5°  | 3398.7 |
| 5°    | 3391.4 |
| 7.5°  | 3358.6 |
| 10°   | 3296.6 |
| 12.5° | 3238.4 |
| 15°   | 3176.5 |
| 17.5° | 3092.7 |
| 20°   | 2983.4 |
| 22.5° | 2863.2 |
| 25°   | 2728.5 |
| 27.5° | 2571.7 |
| 30°   | 2371.4 |
| 32.5° | 2123.7 |
| 35°   | 1792.3 |
| 37.5° | 1431.6 |
| 40°   | 1118.3 |
| 42.5° | 881.5  |
| 45°   | 735.9  |
| 47.5° | 637.5  |
| 50°   | 557.3  |
| 52.5° | 491.8  |
| 55°   | 433.5  |
| 57.5° | 393.4  |
| 60°   | 357.0  |
| 62.5° | 320.5  |
| 65°   | 284.1  |
| 67.5° | 247.7  |
| 70°   | 211.3  |
| 72.5° | 178.4  |
| 75°   | 149.4  |
| 77.5° | 120.2  |
| 80°   | 91.1   |
| 82.5° | 65.5   |
| 85°   | 40.0   |
| 87.5° | 18.2   |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)