

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583714

Luminaire Tested: **HC810D010-HM80520830-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520830-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1147.1 lumens
Efficiency: N/A
Efficacy: 115.9 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583714

CATALOG NUMBER: HC810D010-HM80520830-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583714

CATALOG NUMBER: HC810D010-HM80520830-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99 | 97 | 98 | 96 | 94 | 94 | 93 | 92 | 90 | 90 | 90 | 90 |
| 2 | 104 | 98 | 93 | 89 | 102 | 96 | 92 | 88 | 93 | 89 | 86 | 90 | 87 | 84 | 87 | 84 | 82 | 80 | 80 | 80 | 80 |
| 3 | 98 | 89 | 83 | 78 | 95 | 88 | 82 | 78 | 85 | 80 | 76 | 83 | 78 | 75 | 80 | 77 | 74 | 72 | 72 | 72 | 72 |
| 4 | 91 | 82 | 75 | 70 | 89 | 81 | 74 | 69 | 78 | 73 | 69 | 76 | 72 | 68 | 74 | 70 | 67 | 65 | 65 | 65 | 65 |
| 5 | 86 | 76 | 68 | 63 | 84 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 66 | 62 | 69 | 65 | 61 | 59 | 59 | 59 | 59 |
| 6 | 81 | 70 | 63 | 58 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | 66 | 61 | 56 | 64 | 60 | 56 | 54 | 54 | 54 | 54 |
| 7 | 76 | 65 | 58 | 53 | 74 | 64 | 57 | 53 | 63 | 57 | 52 | 62 | 56 | 52 | 60 | 55 | 52 | 50 | 50 | 50 | 50 |
| 8 | 72 | 61 | 54 | 49 | 70 | 60 | 53 | 49 | 59 | 53 | 48 | 58 | 52 | 48 | 57 | 52 | 48 | 46 | 46 | 46 | 46 |
| 9 | 68 | 57 | 50 | 45 | 67 | 56 | 50 | 45 | 55 | 49 | 45 | 54 | 49 | 45 | 53 | 48 | 45 | 43 | 43 | 43 | 43 |
| 10 | 64 | 53 | 46 | 42 | 63 | 53 | 46 | 42 | 52 | 46 | 42 | 51 | 46 | 42 | 50 | 45 | 42 | 40 | 40 | 40 | 40 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 29328 |
| 5° | 28533 |
| 10° | 26850 |
| 15° | 25421 |
| 20° | 24451 |
| 25° | 23507 |
| 30° | 20876 |
| 35° | 13300 |
| 40° | 7423 |
| 45° | 6219 |
| 50° | 5613 |
| 55° | 5285 |
| 60° | 4829 |
| 65° | 4349 |
| 70° | 3841 |
| 75° | 3407 |
| 80° | 3037 |
| 85° | 2724 |



TEST NUMBER: P583714

CATALOG NUMBER: HC810D010-HM80520830-81MDW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 85.9 | 7.5 |
| 10°-20° | 224.6 | 19.6 |
| 20°-30° | 313.3 | 27.3 |
| 30°-40° | 225.4 | 19.7 |
| 40°-50° | 111.7 | 9.7 |
| 50°-60° | 87.4 | 7.6 |
| 60°-70° | 59.2 | 5.2 |
| 70°-80° | 30.7 | 2.7 |
| 80°-90° | 8.8 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 623.8 | 54.4 |
| 0°-40° | 849.2 | 74.0 |
| 0°-60° | 1048.4 | 91.4 |
| 0°-90° | 1147.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1147.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 951 | |
| 5° | 922 | 86 |
| 15° | 796 | 225 |
| 25° | 691 | 313 |
| 35° | 353 | 225 |
| 45° | 143 | 112 |
| 55° | 98 | 87 |
| 65° | 60 | 59 |
| 75° | 29 | 31 |
| 85° | 8 | 9 |
| 90° | 0 | |



TEST NUMBER: P583714

CATALOG NUMBER: HC810D010-HM80520830-81MDW

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 951.1 |
| 2.5° | 942.6 |
| 5° | 921.8 |
| 7.5° | 892.4 |
| 10° | 857.5 |
| 12.5° | 824.9 |
| 15° | 796.3 |
| 17.5° | 769.2 |
| 20° | 745.1 |
| 22.5° | 721.1 |
| 25° | 690.9 |
| 27.5° | 647.5 |
| 30° | 586.3 |
| 32.5° | 490.3 |
| 35° | 353.3 |
| 37.5° | 240.9 |
| 40° | 184.4 |
| 42.5° | 158.8 |
| 45° | 142.6 |
| 47.5° | 128.6 |
| 50° | 117.0 |
| 52.5° | 106.9 |
| 55° | 98.3 |
| 57.5° | 88.3 |
| 60° | 78.3 |
| 62.5° | 68.2 |
| 65° | 59.6 |
| 67.5° | 51.1 |
| 70° | 42.6 |
| 72.5° | 35.6 |
| 75° | 28.6 |
| 77.5° | 22.5 |
| 80° | 17.1 |
| 82.5° | 12.4 |
| 85° | 7.7 |
| 87.5° | 3.8 |
| 90° | 0.0 |



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)