

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582751

Luminaire Tested: **HC650D010-HM64560835-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560835-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5319.7 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582751

CATALOG NUMBER: HC650D010-HM64560835-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P582751

CATALOG NUMBER: HC650D010-HM64560835-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89			89
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78			78
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69			69
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62			62
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56			56
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51			51
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46			46
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42			42
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39			39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36			36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	181532
5°	181427
10°	179673
15°	177810
20°	172781
25°	165487
30°	153581
35°	132140
40°	96459
45°	66084
50°	53133
55°	46316
60°	42738
65°	40640
70°	37955
75°	35499
80°	32201
85°	27487



TEST NUMBER: P582751

CATALOG NUMBER: HC650D010-HM64560835-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.5	5.9
10°-20°	879.9	16.5
20°-30°	1251.4	23.5
30°-40°	1204.8	22.6
40°-50°	693.2	13.0
50°-60°	439.2	8.3
60°-70°	310.9	5.8
70°-80°	177.3	3.3
80°-90°	50.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2443.8	45.9
0°-40°	3648.6	68.6
0°-60°	4781.0	89.9
0°-90°	5319.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5319.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3311	
5°	3297	313
15°	3133	880
25°	2736	1251
35°	1974	1205
45°	852	693
55°	485	439
65°	313	311
75°	168	177
85°	44	51
90°	0	



TEST NUMBER: P582751

CATALOG NUMBER: HC650D010-HM64560835-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3311.4
2.5°	3296.9
5°	3296.9
7.5°	3275.0
10°	3227.7
12.5°	3180.3
15°	3133.0
17.5°	3060.1
20°	2961.7
22.5°	2852.5
25°	2735.9
27.5°	2593.8
30°	2426.2
32.5°	2222.2
35°	1974.5
37.5°	1672.2
40°	1347.9
42.5°	1063.7
45°	852.4
47.5°	717.7
50°	623.0
52.5°	546.4
55°	484.6
57.5°	429.9
60°	389.8
62.5°	353.4
65°	313.3
67.5°	276.8
70°	236.8
72.5°	200.4
75°	167.6
77.5°	134.8
80°	102.0
82.5°	72.9
85°	43.7
87.5°	18.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)