

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582792

Luminaire Tested: **HC6R50D010-HM64560927-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R50D010-HM64560927-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4231.5 lumens
Efficiency: N/A
Efficacy: 88.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582792

CATALOG NUMBER: HC6R50D010-HM64560927-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582792

CATALOG NUMBER: HC6R50D010-HM64560927-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196273
5°	200572
10°	212610
15°	237652
20°	248825
25°	207466
30°	145193
35°	97781
40°	50366
45°	17490
50°	7787
55°	2561
60°	1173
65°	1038
70°	850
75°	572
80°	852
85°	0



TEST NUMBER: P582792

CATALOG NUMBER: HC6R50D010-HM64560927-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	353.3	8.3
10°-20°	1179.8	27.9
20°-30°	1533.3	36.2
30°-40°	905.7	21.4
40°-50°	216.1	5.1
50°-60°	31.8	0.8
60°-70°	7.9	0.2
70°-80°	3.2	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3066.4	72.5
0°-40°	3972.1	93.9
0°-60°	4220.0	99.7
0°-90°	4231.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4231.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3580	
5°	3645	353
15°	4187	1180
25°	3430	1533
35°	1461	906
45°	226	216
55°	27	32
65°	8	8
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P582792

CATALOG NUMBER: HC6R50D010-HM64560927-62RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	3580.3
2.5°	3588.4
5°	3644.8
7.5°	3717.3
10°	3819.4
12.5°	3980.6
15°	4187.4
17.5°	4327.1
20°	4265.2
22.5°	3953.6
25°	3429.9
27.5°	2831.0
30°	2293.7
32.5°	1855.9
35°	1461.1
37.5°	1074.4
40°	703.8
42.5°	384.1
45°	225.6
47.5°	139.7
50°	91.3
52.5°	53.7
55°	26.8
57.5°	13.5
60°	10.7
62.5°	10.7
65°	8.0
67.5°	5.3
70°	5.3
72.5°	2.7
75°	2.7
77.5°	2.7
80°	2.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)