

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583740

Luminaire Tested: **HC810D010-HM80520835-81WDH**

Issue Date: 10/21/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 10/21/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC810D010-HM80520835-81WDH  
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1282.0 lumens  
Efficiency: N/A  
Efficacy: 129.5 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583740

CATALOG NUMBER: HC810D010-HM80520835-81WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P583740

CATALOG NUMBER: HC810D010-HM80520835-81WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29347
5°	28691
10°	27811
15°	27244
20°	27004
25°	26600
30°	25195
35°	20930
40°	12330
45°	8155
50°	6419
55°	4726
60°	3281
65°	1999
70°	866
75°	381
80°	284
85°	0



TEST NUMBER: P583740

CATALOG NUMBER: HC810D010-HM80520835-81WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.3	6.8
10°-20°	241.3	18.8
20°-30°	357.5	27.9
30°-40°	330.3	25.8
40°-50°	152.3	11.9
50°-60°	80.1	6.3
60°-70°	28.3	2.2
70°-80°	4.4	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.1	53.5
0°-40°	1016.4	79.3
0°-60°	1248.9	97.4
0°-90°	1282.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1282.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	952	
5°	927	87
15°	853	241
25°	782	357
35°	556	330
45°	187	152
55°	88	80
65°	27	28
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P583740

CATALOG NUMBER: HC810D010-HM80520835-81WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	951.7
2.5°	943.7
5°	926.9
7.5°	908.2
10°	888.2
12.5°	868.8
15°	853.4
17.5°	839.7
20°	822.9
22.5°	804.3
25°	781.8
27.5°	751.1
30°	707.6
32.5°	645.6
35°	556.0
37.5°	427.2
40°	306.3
42.5°	229.7
45°	187.0
47.5°	158.8
50°	133.8
52.5°	109.6
55°	87.9
57.5°	69.4
60°	53.2
62.5°	40.3
65°	27.4
67.5°	16.1
70°	9.6
72.5°	5.6
75°	3.2
77.5°	2.4
80°	1.6
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)