

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582780

Luminaire Tested: **HC650D010-HM64560927-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582780  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC650D010-HM64560927-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3654.3 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582780

CATALOG NUMBER: HC650D010-HM64560927-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582780

CATALOG NUMBER: HC650D010-HM64560927-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	138404
5°	137750
10°	134711
15°	131550
20°	126606
25°	119735
30°	108808
35°	88077
40°	59397
45°	40818
50°	33440
55°	29265
60°	27684
65°	26138
70°	24539
75°	23320
80°	21215
85°	18555



TEST NUMBER: P582780

CATALOG NUMBER: HC650D010-HM64560927-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	236.3	6.5
10°-20°	650.9	17.8
20°-30°	904.4	24.7
30°-40°	805.2	22.0
40°-50°	427.4	11.7
50°-60°	279.5	7.6
60°-70°	200.3	5.5
70°-80°	116.2	3.2
80°-90°	34.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1791.6	49.0
0°-40°	2596.8	71.1
0°-60°	3303.8	90.4
0°-90°	3654.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3654.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2525	
5°	2503	236
15°	2318	651
25°	1980	904
35°	1316	805
45°	526	427
55°	306	280
65°	202	200
75°	110	116
85°	30	34
90°	0	



TEST NUMBER: P582780

CATALOG NUMBER: HC650D010-HM64560927-61NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2524.7
2.5°	2511.4
5°	2503.2
7.5°	2473.7
10°	2420.0
12.5°	2371.7
15°	2317.9
17.5°	2250.9
20°	2170.2
22.5°	2078.9
25°	1979.5
27.5°	1864.1
30°	1718.9
32.5°	1544.4
35°	1316.1
37.5°	1063.6
40°	830.0
42.5°	644.6
45°	526.5
47.5°	448.5
50°	392.1
52.5°	346.5
55°	306.2
57.5°	276.7
60°	252.5
62.5°	228.3
65°	201.5
67.5°	177.3
70°	153.1
72.5°	131.6
75°	110.1
77.5°	88.7
80°	67.2
82.5°	48.3
85°	29.5
87.5°	13.5
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)