

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582798

Luminaire Tested: **HC650D010-HM64560930-61NDW**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582798  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-3)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC650D010-HM64560930-61NDW  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4365.8 lumens  
Efficiency: N/A  
Efficacy: 91.0 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.03  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 48  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582798

CATALOG NUMBER: HC650D010-HM64560930-61NDW

### Luminous Intensity Polar Plot





TEST NUMBER: P582798

CATALOG NUMBER: HC650D010-HM64560930-61NDW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	83	86	83	81	79			79
3	97	88	82	77	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	81	73	68	88	79	73	68	77	71	67	75	70	66	73	69	65	63			63
5	84	74	67	61	83	73	66	61	71	65	60	69	64	60	67	63	59	57			57
6	79	68	61	55	77	67	60	55	66	59	55	64	59	54	63	58	54	52			52
7	74	63	56	50	73	62	55	50	61	55	50	60	54	50	58	53	49	48			48
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44			44
9	66	55	48	43	65	54	47	43	53	47	42	52	46	42	51	46	42	41			41
10	62	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	165354
5°	164571
10°	160941
15°	157163
20°	151260
25°	143053
30°	129995
35°	105230
40°	70962
45°	48757
50°	39956
55°	34962
60°	33068
65°	31223
70°	29316
75°	27874
80°	25319
85°	22203



TEST NUMBER: P582798

CATALOG NUMBER: HC650D010-HM64560930-61NDW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	282.3	6.5
10°-20°	777.7	17.8
20°-30°	1080.4	24.7
30°-40°	962.0	22.0
40°-50°	510.7	11.7
50°-60°	334.0	7.6
60°-70°	239.3	5.5
70°-80°	138.8	3.2
80°-90°	40.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2140.4	49.0
0°-40°	3102.4	71.1
0°-60°	3947.0	90.4
0°-90°	4365.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4365.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3016	
5°	2991	282
15°	2769	778
25°	2365	1080
35°	1572	962
45°	629	511
55°	366	334
65°	241	239
75°	132	139
85°	35	41
90°	0	



TEST NUMBER: P582798

CATALOG NUMBER: HC650D010-HM64560930-61NDW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3016.3
2.5°	3000.3
5°	2990.6
7.5°	2955.3
10°	2891.2
12.5°	2833.5
15°	2769.2
17.5°	2689.0
20°	2592.8
22.5°	2483.6
25°	2365.0
27.5°	2226.9
30°	2053.6
32.5°	1845.1
35°	1572.4
37.5°	1270.8
40°	991.6
42.5°	770.1
45°	628.9
47.5°	535.9
50°	468.5
52.5°	413.9
55°	365.8
57.5°	330.6
60°	301.6
62.5°	272.8
65°	240.7
67.5°	211.8
70°	182.9
72.5°	157.2
75°	131.6
77.5°	105.9
80°	80.2
82.5°	57.8
85°	35.3
87.5°	16.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)