

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593519

Luminaire Tested: **HC810D010-HM80520850-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520850-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1172.0 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593519

CATALOG NUMBER: HC810D010-HM80520850-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593519

CATALOG NUMBER: HC810D010-HM80520850-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			
3	104	99	94	91	102	97	93	90	95	91	88	92	90	87	90	88	86	84			
4	100	93	88	84	98	92	88	84	90	86	83	88	85	82	86	83	81	80			
5	96	88	83	79	94	87	82	79	86	81	78	84	80	77	82	79	77	75			
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72			
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65			
9	81	72	67	64	80	72	67	63	71	66	63	70	66	63	69	66	63	62			
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93271
5°	79020
10°	57332
15°	43053
20°	33970
25°	27400
30°	20303
35°	8225
40°	3470
45°	1862
50°	835
55°	419
60°	265
65°	190
70°	153
75°	95
80°	142
85°	283



TEST NUMBER: P593519

CATALOG NUMBER: HC810D010-HM80520850-81NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.2	18.7
10°-20°	378.8	32.3
20°-30°	366.2	31.2
30°-40°	160.8	13.7
40°-50°	34.8	3.0
50°-60°	7.8	0.7
60°-70°	2.7	0.2
70°-80°	1.0	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	964.2	82.3
0°-40°	1125.0	96.0
0°-60°	1167.6	99.6
0°-90°	1172.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1172.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3025	
5°	2553	219
15°	1349	379
25°	805	366
35°	218	161
45°	43	35
55°	8	8
65°	3	3
75°	1	1
85°	1	1
90°	0	



TEST NUMBER: P593519

CATALOG NUMBER: HC810D010-HM80520850-81NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3024.7
1°	3002.0
2°	2940.2
3°	2828.8
4°	2695.6
5°	2552.8
6°	2396.9
7°	2240.2
8°	2093.0
9°	1956.4
10°	1831.0
11°	1712.6
12°	1606.4
13°	1509.7
14°	1424.4
15°	1348.6
17.5°	1178.9
20°	1035.2
22.5°	909.0
25°	805.3
27.5°	700.0
30°	570.2
32.5°	387.4
35°	218.5
37.5°	128.9
40°	86.2
42.5°	60.9
45°	42.7
47.5°	27.9
50°	17.4
52.5°	10.5
55°	7.8
57.5°	6.1
60°	4.3
62.5°	3.5
65°	2.6
67.5°	1.7
70°	1.7
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.8



TEST NUMBER: P593519

CATALOG NUMBER: HC810D010-HM80520850-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







85°		0.8
87.5°		0.8



(END OF REPORT)