

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583793

Luminaire Tested: **HC810D010-HM80520930-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583793
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520930-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1153.3 lumens
Efficiency: N/A
Efficacy: 116.5 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583793

CATALOG NUMBER: HC810D010-HM80520930-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583793

CATALOG NUMBER: HC810D010-HM80520930-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20256
5°	20114
10°	20065
15°	20591
20°	22291
25°	23895
30°	23365
35°	19451
40°	11951
45°	8277
50°	6313
55°	4140
60°	2596
65°	1941
70°	1965
75°	2252
80°	2504
85°	2229



TEST NUMBER: P583793

CATALOG NUMBER: HC810D010-HM80520930-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.7	5.4
10°-20°	185.2	16.1
20°-30°	318.7	27.6
30°-40°	308.8	26.8
40°-50°	152.1	13.2
50°-60°	71.8	6.2
60°-70°	28.3	2.5
70°-80°	19.5	1.7
80°-90°	7.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	565.6	49.0
0°-40°	874.4	75.8
0°-60°	1098.2	95.2
0°-90°	1153.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	657	
5°	650	62
15°	645	185
25°	702	319
35°	517	309
45°	190	152
55°	77	72
65°	27	28
75°	19	20
85°	6	7
90°	0	



TEST NUMBER: P583793

CATALOG NUMBER: HC810D010-HM80520930-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	656.9
2.5°	654.7
5°	649.8
7.5°	645.0
10°	640.8
12.5°	640.1
15°	645.0
17.5°	659.7
20°	679.3
22.5°	696.8
25°	702.3
27.5°	689.7
30°	656.2
32.5°	600.9
35°	516.7
37.5°	401.2
40°	296.9
42.5°	230.4
45°	189.8
47.5°	159.6
50°	131.6
52.5°	103.6
55°	77.0
57.5°	56.0
60°	42.1
62.5°	32.9
65°	26.6
67.5°	23.1
70°	21.8
72.5°	20.3
75°	18.9
77.5°	16.8
80°	14.1
82.5°	10.5
85°	6.3
87.5°	2.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)