

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582920

Luminaire Tested: **HC605D010-HM60525927-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582920
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC605D010-HM60525927-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 531.2 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582920

CATALOG NUMBER: HC605D010-HM60525927-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P582920

CATALOG NUMBER: HC605D010-HM60525927-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26604
5°	26585
10°	26308
15°	25772
20°	24420
25°	22048
30°	18731
35°	13833
40°	8001
45°	4249
50°	2397
55°	1252
60°	822
65°	584
70°	417
75°	318
80°	253
85°	189



TEST NUMBER: P582920

CATALOG NUMBER: HC605D010-HM60525927-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	8.6
10°-20°	127.0	23.9
20°-30°	165.8	31.2
30°-40°	126.7	23.9
40°-50°	45.9	8.6
50°-60°	13.3	2.5
60°-70°	4.7	0.9
70°-80°	1.6	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.6	63.7
0°-40°	465.3	87.6
0°-60°	524.5	98.7
0°-90°	531.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	531.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	485	
5°	483	46
15°	454	127
25°	364	166
35°	207	127
45°	55	46
55°	13	13
65°	4	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582920

CATALOG NUMBER: HC605D010-HM60525927-61MDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	485.3
2.5°	483.1
5°	483.1
7.5°	479.7
10°	472.6
12.5°	464.3
15°	454.1
17.5°	439.1
20°	418.6
22.5°	393.0
25°	364.5
27.5°	332.3
30°	295.9
32.5°	255.0
35°	206.7
37.5°	156.1
40°	111.8
42.5°	77.3
45°	54.8
47.5°	39.3
50°	28.1
52.5°	19.9
55°	13.1
57.5°	9.4
60°	7.5
62.5°	6.0
65°	4.5
67.5°	3.7
70°	2.6
72.5°	1.9
75°	1.5
77.5°	1.1
80°	0.8
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)