

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583803

Luminaire Tested: **HC810D010-HM80520935-81PSMDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583803
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520935-81PSMDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1099.7 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.97
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583803

CATALOG NUMBER: HC810D010-HM80520935-81PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583803

CATALOG NUMBER: HC810D010-HM80520935-81PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89			89
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79			79
3	97	89	83	77	95	87	82	77	85	80	76	82	78	74	80	76	73	71			71
4	91	81	74	69	89	80	74	69	78	72	68	76	71	67	74	70	66	64			64
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58			58
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	60	55	51	49			49
8	71	60	53	48	70	59	52	48	58	52	47	57	51	47	56	51	47	45			45
9	67	56	49	44	66	55	49	44	54	48	44	53	48	44	52	47	44	42			42
10	64	52	46	41	62	52	45	41	51	45	41	50	45	41	49	44	41	39			39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25813
5°	25475
10°	24542
15°	23582
20°	22931
25°	22238
30°	19958
35°	13081
40°	7234
45°	6027
50°	5502
55°	5247
60°	4878
65°	4422
70°	4003
75°	3610
80°	3285
85°	3149



TEST NUMBER: P583803

CATALOG NUMBER: HC810D010-HM80520935-81PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.3	7.0
10°-20°	208.4	19.0
20°-30°	296.6	27.0
30°-40°	219.5	20.0
40°-50°	108.7	9.9
50°-60°	86.8	7.9
60°-70°	60.2	5.5
70°-80°	32.5	3.0
80°-90°	9.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	582.3	53.0
0°-40°	801.9	72.9
0°-60°	997.4	90.7
0°-90°	1099.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1099.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	837	
5°	823	77
15°	739	208
25°	654	297
35°	348	220
45°	138	109
55°	98	87
65°	61	60
75°	30	32
85°	9	10
90°	0	



TEST NUMBER: P583803

CATALOG NUMBER: HC810D010-HM80520935-81PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	837.1
2.5°	833.3
5°	823.0
7.5°	806.8
10°	783.8
12.5°	760.1
15°	738.7
17.5°	718.1
20°	698.8
22.5°	679.6
25°	653.6
27.5°	616.0
30°	560.5
32.5°	475.5
35°	347.5
37.5°	237.4
40°	179.7
42.5°	153.9
45°	138.2
47.5°	125.7
50°	114.7
52.5°	105.1
55°	97.6
57.5°	88.7
60°	79.1
62.5°	69.5
65°	60.6
67.5°	51.8
70°	44.4
72.5°	37.0
75°	30.3
77.5°	24.4
80°	18.5
82.5°	13.3
85°	8.9
87.5°	3.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)