

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593007

Luminaire Tested: **HC605D010-HM60525950-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC605D010-HM60525950-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 602.3 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593007

CATALOG NUMBER: HC605D010-HM60525950-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P593007

CATALOG NUMBER: HC605D010-HM60525950-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	50	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22427
5°	22342
10°	21971
15°	21578
20°	20838
25°	19761
30°	17971
35°	14362
40°	9582
45°	6830
50°	5689
55°	4960
60°	4682
65°	4410
70°	4055
75°	3791
80°	3410
85°	2956



TEST NUMBER: P593007

CATALOG NUMBER: HC605D010-HM60525950-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.4	6.4
10°-20°	106.8	17.7
20°-30°	149.2	24.8
30°-40°	131.4	21.8
40°-50°	71.0	11.8
50°-60°	47.5	7.9
60°-70°	33.6	5.6
70°-80°	18.9	3.1
80°-90°	5.4	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.4	48.9
0°-40°	425.8	70.7
0°-60°	544.3	90.4
0°-90°	602.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	409	
5°	406	38
15°	380	107
25°	327	149
35°	215	131
45°	88	71
55°	52	47
65°	34	34
75°	18	19
85°	5	5
90°	0	



TEST NUMBER: P593007

CATALOG NUMBER: HC605D010-HM60525950-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	409.1
2.5°	406.9
5°	406.0
7.5°	402.1
10°	394.7
12.5°	387.7
15°	380.2
17.5°	370.3
20°	357.2
22.5°	342.7
25°	326.7
27.5°	307.9
30°	283.9
32.5°	254.2
35°	214.6
37.5°	171.4
40°	133.9
42.5°	105.5
45°	88.1
47.5°	76.3
50°	66.7
52.5°	58.9
55°	51.9
57.5°	47.1
60°	42.7
62.5°	38.4
65°	34.0
67.5°	29.6
70°	25.3
72.5°	21.4
75°	17.9
77.5°	14.4
80°	10.8
82.5°	7.8
85°	4.7
87.5°	2.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)