

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583840

Luminaire Tested: **HC815D010-HM80520827-81WDBB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520827-81WDBB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1601.5 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583840

CATALOG NUMBER: HC815D010-HM80520827-81WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P583840

CATALOG NUMBER: HC815D010-HM80520827-81WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			
5	87	77	71	66	85	76	70	65	74	69	65	73	68	64	71	67	63	62			
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	41	50	45	41	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30004
5°	29753
10°	29361
15°	29699
20°	32070
25°	35072
30°	34645
35°	28741
40°	16915
45°	11051
50°	8568
55°	5688
60°	2769
65°	861
70°	298
75°	262
80°	195
85°	389



TEST NUMBER: P583840

CATALOG NUMBER: HC815D010-HM80520827-81WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	5.7
10°-20°	267.3	16.7
20°-30°	467.3	29.2
30°-40°	454.5	28.4
40°-50°	206.7	12.9
50°-60°	95.8	6.0
60°-70°	16.1	1.0
70°-80°	2.0	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	825.5	51.5
0°-40°	1280.1	79.9
0°-60°	1582.6	98.8
0°-90°	1601.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1601.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	973	
5°	961	91
15°	930	267
25°	1031	467
35°	764	455
45°	253	207
55°	106	96
65°	12	16
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P583840

CATALOG NUMBER: HC815D010-HM80520827-81WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	973.0
2.5°	970.9
5°	961.2
7.5°	950.5
10°	937.7
12.5°	928.1
15°	930.3
17.5°	947.4
20°	977.3
22.5°	1011.5
25°	1030.8
27.5°	1020.0
30°	973.0
32.5°	890.6
35°	763.5
37.5°	588.0
40°	420.2
42.5°	313.3
45°	253.4
47.5°	213.9
50°	178.6
52.5°	142.2
55°	105.8
57.5°	72.7
60°	44.9
62.5°	24.6
65°	11.8
67.5°	5.3
70°	3.3
72.5°	2.2
75°	2.2
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)