

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583010

Luminaire Tested: **HC655D010-HM64560830-61MDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560830-61MDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5175.6 lumens
Efficiency: N/A
Efficacy: 99.5 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 0.97
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583010

CATALOG NUMBER: HC655D010-HM64560830-61MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583010

CATALOG NUMBER: HC655D010-HM64560830-61MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	96	88	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	71	89	80	75	70	79	74	70	77	73	69	75	72	68	67	67	67	67
6	85	76	70	65	84	75	69	65	74	68	64	72	67	64	71	67	63	62	62	62	62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57	57	57	57
8	77	67	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53	53	53	53
9	73	62	56	52	72	62	56	52	61	56	52	60	55	52	59	55	51	50	50	50	50
10	69	59	53	49	68	58	52	48	57	52	48	57	52	48	56	51	48	47	47	47	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	259217
5°	258991
10°	256291
15°	251142
20°	237904
25°	214839
30°	182503
35°	134750
40°	77932
45°	41361
50°	23377
55°	12224
60°	8015
65°	5695
70°	4103
75°	3114
80°	2305
85°	2327



TEST NUMBER: P583010

CATALOG NUMBER: HC655D010-HM64560830-61MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	446.0	8.6
10°-20°	1237.7	23.9
20°-30°	1615.4	31.2
30°-40°	1234.5	23.9
40°-50°	446.9	8.6
50°-60°	129.8	2.5
60°-70°	46.4	0.9
70°-80°	15.9	0.3
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3299.1	63.7
0°-40°	4533.6	87.6
0°-60°	5110.3	98.7
0°-90°	5175.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5175.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4728	
5°	4706	446
15°	4425	1238
25°	3552	1615
35°	2014	1234
45°	534	447
55°	128	130
65°	44	46
75°	15	16
85°	4	3
90°	0	



TEST NUMBER: P583010

CATALOG NUMBER: HC655D010-HM64560830-61MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	4728.5
2.5°	4706.4
5°	4706.4
7.5°	4673.6
10°	4604.1
12.5°	4523.8
15°	4425.1
17.5°	4278.9
20°	4078.0
22.5°	3829.5
25°	3551.8
27.5°	3237.5
30°	2883.1
32.5°	2484.8
35°	2013.5
37.5°	1520.2
40°	1089.0
42.5°	752.7
45°	533.5
47.5°	383.6
50°	274.1
52.5°	193.7
55°	127.9
57.5°	91.3
60°	73.1
62.5°	58.4
65°	43.9
67.5°	36.6
70°	25.6
72.5°	18.2
75°	14.7
77.5°	11.0
80°	7.3
82.5°	3.7
85°	3.7
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)