

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583009

Luminaire Tested: **HC655D010-HM64560830-61MDC**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583009  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC655D010-HM64560830-61MDC  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5760.0 lumens  
Efficiency: N/A  
Efficacy: 110.8 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583009

CATALOG NUMBER: HC655D010-HM64560830-61MDC

### Luminous Intensity Polar Plot





TEST NUMBER: P583009

CATALOG NUMBER: HC655D010-HM64560830-61MDC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	273525
5°	277789
10°	293604
15°	326920
20°	339028
25°	278163
30°	194916
35°	132983
40°	69265
45°	24351
50°	10908
55°	3498
60°	1995
65°	1427
70°	1170
75°	784
80°	0
85°	0



TEST NUMBER: P583009

CATALOG NUMBER: HC655D010-HM64560830-61MDC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	489.0	8.5
10°-20°	1620.0	28.1
20°-30°	2062.7	35.8
30°-40°	1229.3	21.3
40°-50°	298.1	5.2
50°-60°	45.8	0.8
60°-70°	11.3	0.2
70°-80°	3.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4171.7	72.4
0°-40°	5401.0	93.8
0°-60°	5744.9	99.7
0°-90°	5760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5760.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4990	
5°	5048	489
15°	5760	1620
25°	4599	2063
35°	1987	1229
45°	314	298
55°	37	46
65°	11	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P583009

CATALOG NUMBER: HC655D010-HM64560830-61MDC

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4989.5
2.5°	4989.5
5°	5048.0
7.5°	5139.3
10°	5274.4
12.5°	5486.3
15°	5760.3
17.5°	5931.9
20°	5811.4
22.5°	5347.5
25°	4598.7
27.5°	3773.2
30°	3079.2
32.5°	2516.7
35°	1987.1
37.5°	1464.7
40°	967.9
42.5°	522.3
45°	314.1
47.5°	197.2
50°	127.9
52.5°	76.7
55°	36.6
57.5°	21.9
60°	18.2
62.5°	14.7
65°	11.0
67.5°	7.3
70°	7.3
72.5°	3.7
75°	3.7
77.5°	3.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)