

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583834

Luminaire Tested: **HC815D010-HM80520827-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583834
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520827-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1587.6 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583834

CATALOG NUMBER: HC815D010-HM80520827-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583834

CATALOG NUMBER: HC815D010-HM80520827-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	108	112	110	108	106	106	105	103	102	101	100	99	98	97	96			96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91			91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87			87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83			83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80			80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76			76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73			73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68			68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66			66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298798
5°	191652
10°	86578
15°	52237
20°	39808
25°	32146
30°	23554
35°	8526
40°	3180
45°	1443
50°	461
55°	118
60°	68
65°	80
70°	0
75°	0
80°	195
85°	389



TEST NUMBER: P583834

CATALOG NUMBER: HC815D010-HM80520827-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	472.2	29.7
10°-20°	479.6	30.2
20°-30°	429.4	27.0
30°-40°	172.9	10.9
40°-50°	28.4	1.8
50°-60°	2.6	0.2
60°-70°	1.0	0.1
70°-80°	0.7	0.0
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1381.2	87.0
0°-40°	1554.1	97.9
0°-60°	1585.1	99.8
0°-90°	1587.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1587.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9690	
5°	6192	472
15°	1636	480
25°	945	429
35°	226	173
45°	33	28
55°	2	3
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P583834

CATALOG NUMBER: HC815D010-HM80520827-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	9689.8
0.5°	9659.8
1°	9534.7
1.5°	9333.8
2°	9029.2
2.5°	8669.0
3°	8218.0
3.5°	7723.1
4°	7233.6
4.5°	6685.3
5°	6191.5
5.5°	5654.0
6°	5217.9
6.5°	4763.6
7°	4406.7
7.5°	4029.4
8°	3725.9
8.5°	3421.2
9°	3192.5
9.5°	2940.2
10°	2765.0
12.5°	2039.2
15°	1636.3
17.5°	1398.0
20°	1213.1
22.5°	1065.6
25°	944.8
27.5°	824.1
30°	661.5
32.5°	425.4
35°	226.5
37.5°	125.1
40°	79.0
42.5°	52.4
45°	33.1
47.5°	20.4
50°	9.6
52.5°	3.3
55°	2.2
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1



TEST NUMBER: P583834

CATALOG NUMBER: HC815D010-HM80520827-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.1
80°	1.1
82.5°	1.1
85°	1.1
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		<i>1.1</i>
70°		<i>0.0</i>



(END OF REPORT)