

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593551

Luminaire Tested: **HC815D010-HM80520850-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593551
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520850-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1957.3 lumens
Efficiency: N/A
Efficacy: 139.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593551

CATALOG NUMBER: HC815D010-HM80520850-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P593551

CATALOG NUMBER: HC815D010-HM80520850-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81			81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59			59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54			54
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49			49
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45			45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41			41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34373
5°	34136
10°	34049
15°	34941
20°	37826
25°	40557
30°	39648
35°	33014
40°	20284
45°	14047
50°	10717
55°	7027
60°	4397
65°	3298
70°	3327
75°	3824
80°	4209
85°	3786



TEST NUMBER: P593551

CATALOG NUMBER: HC815D010-HM80520850-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.8	5.4
10°-20°	314.2	16.1
20°-30°	540.9	27.6
30°-40°	524.0	26.8
40°-50°	258.1	13.2
50°-60°	121.8	6.2
60°-70°	48.0	2.5
70°-80°	33.1	1.7
80°-90°	12.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	959.9	49.0
0°-40°	1483.9	75.8
0°-60°	1863.8	95.2
0°-90°	1957.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1957.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1115	
5°	1103	105
15°	1094	314
25°	1192	541
35°	877	524
45°	322	258
55°	131	122
65°	45	48
75°	32	33
85°	11	12
90°	0	



TEST NUMBER: P593551

CATALOG NUMBER: HC815D010-HM80520850-81WDWB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1114.7
2.5°	1111.1
5°	1102.8
7.5°	1094.5
10°	1087.4
12.5°	1086.2
15°	1094.5
17.5°	1119.4
20°	1152.7
22.5°	1182.5
25°	1192.0
27.5°	1170.5
30°	1113.5
32.5°	1019.7
35°	877.0
37.5°	680.9
40°	503.9
42.5°	391.0
45°	322.1
47.5°	271.0
50°	223.4
52.5°	175.9
55°	130.7
57.5°	95.1
60°	71.3
62.5°	55.9
65°	45.2
67.5°	39.2
70°	36.9
72.5°	34.5
75°	32.1
77.5°	28.6
80°	23.7
82.5°	17.8
85°	10.7
87.5°	4.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)