

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583092

Luminaire Tested: **HC655D010-HM64560930-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583092  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC655D010-HM64560930-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4969.1 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583092

CATALOG NUMBER: HC655D010-HM64560930-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P583092

CATALOG NUMBER: HC655D010-HM64560930-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	194617
5°	195911
10°	198176
15°	202237
20°	203379
25°	197038
30°	178749
35°	145344
40°	96466
45°	53688
50°	30106
55°	16707
60°	9210
65°	6979
70°	4857
75°	3558
80°	2115
85°	2076



TEST NUMBER: P583092

CATALOG NUMBER: HC655D010-HM64560930-61WDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	339.8	6.8
10°-20°	1004.8	20.2
20°-30°	1480.9	29.8
30°-40°	1324.6	26.7
40°-50°	574.6	11.6
50°-60°	168.8	3.4
60°-70°	53.9	1.1
70°-80°	19.0	0.4
80°-90°	2.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2825.5	56.9
0°-40°	4150.1	83.5
0°-60°	4893.5	98.5
0°-90°	4969.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4969.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3550	
5°	3560	340
15°	3563	1005
25°	3258	1481
35°	2172	1325
45°	692	575
55°	175	169
65°	54	54
75°	17	19
85°	3	3
90°	0	



TEST NUMBER: P583092

CATALOG NUMBER: HC655D010-HM64560930-61WDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3550.1
2.5°	3539.9
5°	3560.1
7.5°	3566.9
10°	3560.1
12.5°	3560.1
15°	3563.4
17.5°	3543.3
20°	3486.2
22.5°	3388.7
25°	3257.5
27.5°	3072.6
30°	2823.8
32.5°	2528.1
35°	2171.8
37.5°	1764.9
40°	1348.0
42.5°	985.0
45°	692.5
47.5°	494.1
50°	353.0
52.5°	252.1
55°	174.8
57.5°	117.7
60°	84.0
62.5°	67.2
65°	53.8
67.5°	40.3
70°	30.3
72.5°	23.5
75°	16.8
77.5°	13.5
80°	6.7
82.5°	3.3
85°	3.3
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)