

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583110

Luminaire Tested: **HC655D010-HM64560935-61WDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560935-61WDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5027.6 lumens
Efficiency: N/A
Efficacy: 96.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583110

CATALOG NUMBER: HC655D010-HM64560935-61WDH

Luminous Intensity Polar Plot





TEST NUMBER: P583110

CATALOG NUMBER: HC655D010-HM64560935-61WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	92	90	93	90	88	90	88	86	84	84	84	84
3	100	93	87	83	98	91	86	82	89	84	81	86	83	80	84	81	78	77	77	77	77
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59	59	59	59
7	79	68	62	57	77	68	61	57	66	60	56	65	60	56	64	59	56	54	54	54	54
8	74	64	57	52	73	63	57	52	62	56	52	61	56	52	60	55	51	50	50	50	50
9	70	59	53	48	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	53	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	196898
5°	198211
10°	200503
15°	204615
20°	205765
25°	199354
30°	180857
35°	147043
40°	97604
45°	54323
50°	30455
55°	16907
60°	9330
65°	7057
70°	4905
75°	3601
80°	2178
85°	2139



TEST NUMBER: P583110

CATALOG NUMBER: HC655D010-HM64560935-61WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.8	6.8
10°-20°	1016.6	20.2
20°-30°	1498.3	29.8
30°-40°	1340.1	26.7
40°-50°	581.4	11.6
50°-60°	170.8	3.4
60°-70°	54.5	1.1
70°-80°	19.3	0.4
80°-90°	2.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2858.7	56.9
0°-40°	4198.8	83.5
0°-60°	4951.0	98.5
0°-90°	5027.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5027.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3592	
5°	3602	344
15°	3605	1017
25°	3296	1498
35°	2197	1340
45°	701	581
55°	177	171
65°	54	55
75°	17	19
85°	3	3
90°	0	



TEST NUMBER: P583110

CATALOG NUMBER: HC655D010-HM64560935-61WDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3591.7
2.5°	3581.5
5°	3601.9
7.5°	3608.7
10°	3601.9
12.5°	3601.9
15°	3605.3
17.5°	3585.0
20°	3527.1
22.5°	3428.5
25°	3295.8
27.5°	3108.7
30°	2857.1
32.5°	2557.8
35°	2197.2
37.5°	1785.6
40°	1363.9
42.5°	996.6
45°	700.7
47.5°	499.9
50°	357.1
52.5°	255.1
55°	176.9
57.5°	119.0
60°	85.1
62.5°	68.0
65°	54.4
67.5°	40.8
70°	30.6
72.5°	23.8
75°	17.0
77.5°	13.6
80°	6.9
82.5°	3.4
85°	3.4
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)