

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583936

Luminaire Tested: **HC815D010-HM80520935-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583936
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520935-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1507.4 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583936

CATALOG NUMBER: HC815D010-HM80520935-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583936

CATALOG NUMBER: HC815D010-HM80520935-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	96	96	96
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91	91	91	91
3	106	101	97	93	104	99	96	93	97	94	91	95	92	90	92	90	89	87	87	87	87
4	102	96	91	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83	83	83	83
5	98	92	87	83	97	91	86	83	89	85	82	87	84	82	86	83	81	80	80	80	80
6	95	88	83	79	93	87	82	79	86	82	79	84	81	78	83	80	78	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71	71	71	71
9	85	78	73	70	84	77	73	70	76	72	70	76	72	69	75	72	69	68	68	68	68
10	83	75	70	67	82	75	70	67	74	70	67	73	69	67	73	69	67	66	66	66	66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	283734
5°	181992
10°	82213
15°	49604
20°	37803
25°	30526
30°	22372
35°	8101
40°	3023
45°	1374
50°	441
55°	108
60°	62
65°	73
70°	0
75°	0
80°	178
85°	354



TEST NUMBER: P583936

CATALOG NUMBER: HC815D010-HM80520935-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	448.4	29.7
10°-20°	455.5	30.2
20°-30°	407.7	27.0
30°-40°	164.2	10.9
40°-50°	27.0	1.8
50°-60°	2.4	0.2
60°-70°	0.9	0.1
70°-80°	0.7	0.0
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1311.6	87.0
0°-40°	1475.8	97.9
0°-60°	1505.2	99.9
0°-90°	1507.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1507.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9201	
5°	5879	448
15°	1554	455
25°	897	408
35°	215	164
45°	32	27
55°	2	2
65°	1	1
75°	0	1
85°	1	1
90°	0	



TEST NUMBER: P583936

CATALOG NUMBER: HC815D010-HM80520935-81NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	9201.3
0.5°	9172.8
1°	9054.1
1.5°	8863.3
2°	8574.1
2.5°	8232.1
3°	7803.7
3.5°	7333.9
4°	6869.0
4.5°	6348.3
5°	5879.4
5.5°	5369.0
6°	4954.8
6.5°	4523.4
7°	4184.5
7.5°	3826.2
8°	3538.0
8.5°	3248.8
9°	3031.5
9.5°	2792.1
10°	2625.6
12.5°	1936.4
15°	1553.8
17.5°	1327.5
20°	1152.0
22.5°	1011.8
25°	897.2
27.5°	782.5
30°	628.3
32.5°	403.9
35°	215.2
37.5°	118.7
40°	75.1
42.5°	49.8
45°	31.5
47.5°	19.3
50°	9.2
52.5°	3.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0



TEST NUMBER: P583936

CATALOG NUMBER: HC815D010-HM80520935-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	1.0
80°	1.0
82.5°	1.0
85°	1.0
87.5°	1.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







67.5°		1.0
70°		0.0



(END OF REPORT)