

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583192

Luminaire Tested: **HC660D010-HM64560840-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583192
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560840-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6310.7 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583192

CATALOG NUMBER: HC660D010-HM64560840-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583192

CATALOG NUMBER: HC660D010-HM64560840-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94			
2	108	103	99	96	106	102	98	95	98	96	93	96	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	79	83	80	78	76			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71			
6	88	80	74	70	87	79	73	69	77	73	69	76	72	68	75	71	68	67			
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	60	56	55			
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376883
5°	377640
10°	383855
15°	386654
20°	353449
25°	277734
30°	203303
35°	144213
40°	68206
45°	26026
50°	11658
55°	3173
60°	1360
65°	1077
70°	657
75°	868
80°	0
85°	0



TEST NUMBER: P583192

CATALOG NUMBER: HC660D010-HM64560840-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	656.5	10.4
10°-20°	1883.0	29.8
20°-30°	2094.5	33.2
30°-40°	1308.4	20.7
40°-50°	310.9	4.9
50°-60°	44.4	0.7
60°-70°	9.2	0.1
70°-80°	3.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4634.0	73.4
0°-40°	5942.4	94.2
0°-60°	6297.7	99.8
0°-90°	6310.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6310.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6875	
5°	6862	656
15°	6813	1883
25°	4592	2095
35°	2155	1308
45°	336	311
55°	33	44
65°	8	9
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P583192

CATALOG NUMBER: HC660D010-HM64560840-61NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	6874.9
2.5°	6845.9
5°	6862.5
7.5°	6887.3
10°	6895.7
12.5°	6891.4
15°	6812.8
17.5°	6547.5
20°	6058.6
22.5°	5370.7
25°	4591.6
27.5°	3845.7
30°	3211.7
32.5°	2685.3
35°	2154.9
37.5°	1583.0
40°	953.1
42.5°	551.2
45°	335.7
47.5°	215.5
50°	136.7
52.5°	78.7
55°	33.2
57.5°	16.5
60°	12.4
62.5°	12.4
65°	8.3
67.5°	8.3
70°	4.1
72.5°	4.1
75°	4.1
77.5°	4.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)