

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583972

Luminaire Tested: **HC820D010-HM80520827-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583972
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC820D010-HM80520827-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1949.3 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583972

CATALOG NUMBER: HC820D010-HM80520827-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P583972

CATALOG NUMBER: HC820D010-HM80520827-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90			
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48589
5°	48456
10°	47651
15°	46957
20°	45827
25°	43503
30°	35884
35°	18476
40°	12370
45°	10601
50°	9153
55°	7989
60°	7092
65°	6370
70°	5779
75°	5207
80°	4653
85°	4635



TEST NUMBER: P583972

CATALOG NUMBER: HC820D010-HM80520827-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	148.0	7.6
10°-20°	413.8	21.2
20°-30°	573.4	29.4
30°-40°	344.4	17.7
40°-50°	188.5	9.7
50°-60°	134.0	6.9
60°-70°	86.9	4.5
70°-80°	46.5	2.4
80°-90°	13.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.2	58.2
0°-40°	1479.6	75.9
0°-60°	1802.1	92.4
0°-90°	1949.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1949.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1576	
5°	1565	148
15°	1471	414
25°	1279	573
35°	491	344
45°	243	189
55°	149	134
65°	87	87
75°	44	46
85°	13	14
90°	0	



TEST NUMBER: P583972

CATALOG NUMBER: HC820D010-HM80520827-81NDW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1575.7
2.5°	1572.8
5°	1565.4
7.5°	1548.1
10°	1521.8
12.5°	1497.0
15°	1470.9
17.5°	1437.3
20°	1396.5
22.5°	1347.0
25°	1278.6
27.5°	1170.9
30°	1007.8
32.5°	738.3
35°	490.8
37.5°	362.6
40°	307.3
42.5°	272.3
45°	243.1
47.5°	215.5
50°	190.8
52.5°	167.5
55°	148.6
57.5°	131.1
60°	115.0
62.5°	100.5
65°	87.3
67.5°	74.2
70°	64.1
72.5°	52.5
75°	43.7
77.5°	35.0
80°	26.2
82.5°	18.9
85°	13.1
87.5°	5.8
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)