

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583207

Luminaire Tested: **HC660D010-HM64560927-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583207
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560927-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4624.0 lumens
Efficiency: N/A
Efficacy: 84.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583207

CATALOG NUMBER: HC660D010-HM64560927-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P583207

CATALOG NUMBER: HC660D010-HM64560927-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54			
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	219582
5°	223002
10°	235700
15°	262442
20°	272160
25°	223307
30°	156480
35°	106756
40°	55611
45°	19552
50°	8750
55°	2800
60°	1601
65°	1141
70°	946
75°	614
80°	0
85°	0



TEST NUMBER: P583207

CATALOG NUMBER: HC660D010-HM64560927-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	392.5	8.5
10°-20°	1300.5	28.1
20°-30°	1655.9	35.8
30°-40°	986.9	21.3
40°-50°	239.3	5.2
50°-60°	36.7	0.8
60°-70°	9.1	0.2
70°-80°	3.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3348.9	72.4
0°-40°	4335.9	93.8
0°-60°	4611.9	99.7
0°-90°	4624.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4624.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4006	
5°	4052	393
15°	4624	1300
25°	3692	1656
35°	1595	987
45°	252	239
55°	29	37
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P583207

CATALOG NUMBER: HC660D010-HM64560927-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4005.5
2.5°	4005.5
5°	4052.4
7.5°	4125.7
10°	4234.2
12.5°	4404.3
15°	4624.2
17.5°	4762.0
20°	4665.2
22.5°	4292.8
25°	3691.8
27.5°	3029.0
30°	2472.0
32.5°	2020.4
35°	1595.2
37.5°	1175.9
40°	777.1
42.5°	419.3
45°	252.2
47.5°	158.4
50°	102.6
52.5°	61.5
55°	29.3
57.5°	17.6
60°	14.6
62.5°	11.8
65°	8.8
67.5°	5.9
70°	5.9
72.5°	2.9
75°	2.9
77.5°	2.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)