

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583274

Luminaire Tested: **HC660D010-HM64560940-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583274
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560940-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5750.9 lumens
Efficiency: N/A
Efficacy: 104.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583274

CATALOG NUMBER: HC660D010-HM64560940-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583274

CATALOG NUMBER: HC660D010-HM64560940-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			82
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214495
5°	216316
10°	224111
15°	243435
20°	253212
25°	242191
30°	209013
35°	150497
40°	84780
45°	43943
50°	26200
55°	18876
60°	16040
65°	18497
70°	23449
75°	24782
80°	24214
85°	23021



TEST NUMBER: P583274

CATALOG NUMBER: HC660D010-HM64560940-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.2	6.6
10°-20°	1209.8	21.0
20°-30°	1808.2	31.4
30°-40°	1382.2	24.0
40°-50°	482.8	8.4
50°-60°	184.0	3.2
60°-70°	144.3	2.5
70°-80°	122.0	2.1
80°-90°	39.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3396.2	59.1
0°-40°	4778.4	83.1
0°-60°	5445.2	94.7
0°-90°	5750.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5750.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3913	
5°	3931	378
15°	4289	1210
25°	4004	1808
35°	2249	1382
45°	567	483
55°	198	184
65°	143	144
75°	117	122
85°	37	39
90°	0	



TEST NUMBER: P583274

CATALOG NUMBER: HC660D010-HM64560940-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3912.7
2.5°	3901.7
5°	3930.9
7.5°	3971.1
10°	4026.0
12.5°	4150.3
15°	4289.3
17.5°	4373.3
20°	4340.4
22.5°	4208.8
25°	4004.0
27.5°	3711.5
30°	3301.9
32.5°	2812.0
35°	2248.8
37.5°	1667.4
40°	1184.7
42.5°	830.1
45°	566.8
47.5°	398.6
50°	307.2
52.5°	241.3
55°	197.5
57.5°	160.9
60°	146.3
62.5°	142.6
65°	142.6
67.5°	149.9
70°	146.3
72.5°	135.3
75°	117.0
77.5°	98.7
80°	76.7
82.5°	54.9
85°	36.6
87.5°	14.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)