

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P575617

Luminaire Tested: **HC820D010-HM80520835-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P575617
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC820D010-HM80520835-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2434.2 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P575617

CATALOG NUMBER: HC820D010-HM80520835-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P575617

CATALOG NUMBER: HC820D010-HM80520835-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89			89
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84			84
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79			79
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75			75
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71			71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67			67
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64			64
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61			61
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145439
5°	138767
10°	119809
15°	91613
20°	70094
25°	55456
30°	41888
35°	22289
40°	8490
45°	4073
50°	1737
55°	731
60°	278
65°	219
70°	135
75°	0
80°	0
85°	0



TEST NUMBER: P575617

CATALOG NUMBER: HC820D010-HM80520835-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	406.9	16.7
10°-20°	801.1	32.9
20°-30°	746.1	30.7
30°-40°	385.0	15.8
40°-50°	78.4	3.2
50°-60°	13.4	0.6
60°-70°	2.6	0.1
70°-80°	0.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1954.2	80.3
0°-40°	2339.2	96.1
0°-60°	2431.0	99.9
0°-90°	2434.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2434.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4716	
5°	4483	407
15°	2870	801
25°	1630	746
35°	592	385
45°	93	78
55°	14	13
65°	3	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P575617

CATALOG NUMBER: HC820D010-HM80520835-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4716.5
2.5°	4653.2
5°	4483.0
7.5°	4202.8
10°	3826.3
12.5°	3332.2
15°	2869.7
17.5°	2469.0
20°	2136.0
22.5°	1865.0
25°	1629.9
27.5°	1406.9
30°	1176.4
32.5°	902.3
35°	592.1
37.5°	343.5
40°	210.9
42.5°	138.5
45°	93.4
47.5°	58.7
50°	36.2
52.5°	21.0
55°	13.6
57.5°	6.0
60°	4.5
62.5°	3.0
65°	3.0
67.5°	1.5
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)