

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584009

Luminaire Tested: **HC820D010-HM80520835-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC820D010-HM80520835-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2313.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584009

CATALOG NUMBER: HC820D010-HM80520835-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584009

CATALOG NUMBER: HC820D010-HM80520835-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46258
5°	46199
10°	45741
15°	45195
20°	44777
25°	44276
30°	41777
35°	34015
40°	18795
45°	12546
50°	11125
55°	10446
60°	10305
65°	10222
70°	9232
75°	8257
80°	7227
85°	6404



TEST NUMBER: P584009

CATALOG NUMBER: HC820D010-HM80520835-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.5	6.1
10°-20°	399.7	17.3
20°-30°	594.0	25.7
30°-40°	534.9	23.1
40°-50°	237.1	10.2
50°-60°	175.6	7.6
60°-70°	136.6	5.9
70°-80°	74.1	3.2
80°-90°	20.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.2	49.1
0°-40°	1670.0	72.2
0°-60°	2082.8	90.0
0°-90°	2313.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2313.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1500	
5°	1492	141
15°	1416	400
25°	1301	594
35°	904	535
45°	288	237
55°	194	176
65°	140	137
75°	69	74
85°	18	20
90°	0	



TEST NUMBER: P584009

CATALOG NUMBER: HC820D010-HM80520835-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1500.1
2.5°	1497.0
5°	1492.5
7.5°	1480.5
10°	1460.8
12.5°	1438.3
15°	1415.7
17.5°	1393.1
20°	1364.5
22.5°	1335.9
25°	1301.3
27.5°	1248.5
30°	1173.3
32.5°	1064.7
35°	903.6
37.5°	674.7
40°	466.9
42.5°	344.9
45°	287.7
47.5°	254.5
50°	231.9
52.5°	210.9
55°	194.3
57.5°	180.7
60°	167.1
62.5°	155.1
65°	140.1
67.5°	122.0
70°	102.4
72.5°	85.8
75°	69.3
77.5°	54.3
80°	40.7
82.5°	28.6
85°	18.1
87.5°	7.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)