

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583328

Luminaire Tested: **HC607D010-HM60525835-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525835-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1010.0 lumens
Efficiency: N/A
Efficacy: 126.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583328

CATALOG NUMBER: HC607D010-HM60525835-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583328

CATALOG NUMBER: HC607D010-HM60525835-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82			82
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	78	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	65	63			63
6	83	73	66	61	81	72	66	61	70	65	60	69	64	60	67	63	60	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54			54
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	48	45	53	48	44	53	48	44	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37672
5°	37987
10°	39356
15°	42747
20°	44471
25°	42529
30°	36708
35°	26435
40°	14885
45°	7722
50°	4597
55°	3316
60°	2818
65°	3243
70°	4119
75°	4342
80°	4262
85°	4088



TEST NUMBER: P583328

CATALOG NUMBER: HC607D010-HM60525835-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	6.6
10°-20°	212.5	21.0
20°-30°	317.6	31.4
30°-40°	242.8	24.0
40°-50°	84.8	8.4
50°-60°	32.3	3.2
60°-70°	25.3	2.5
70°-80°	21.4	2.1
80°-90°	6.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.4	59.1
0°-40°	839.2	83.1
0°-60°	956.3	94.7
0°-90°	1010.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1010.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	690	66
15°	753	212
25°	703	318
35°	395	243
45°	100	85
55°	35	32
65°	25	25
75°	20	21
85°	6	7
90°	0	



TEST NUMBER: P583328

CATALOG NUMBER: HC607D010-HM60525835-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	687.2
2.5°	685.2
5°	690.3
7.5°	697.4
10°	707.0
12.5°	728.9
15°	753.2
17.5°	768.1
20°	762.3
22.5°	739.2
25°	703.1
27.5°	651.8
30°	579.9
32.5°	493.9
35°	395.0
37.5°	292.9
40°	208.0
42.5°	145.8
45°	99.6
47.5°	70.0
50°	53.9
52.5°	42.4
55°	34.7
57.5°	28.2
60°	25.7
62.5°	25.0
65°	25.0
67.5°	26.3
70°	25.7
72.5°	23.8
75°	20.5
77.5°	17.3
80°	13.5
82.5°	9.6
85°	6.5
87.5°	2.6
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)