

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583332

Luminaire Tested: **HC6R07D010-HM60525835-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R07D010-HM60525835-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1011.9 lumens
Efficiency: N/A
Efficacy: 126.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583332

CATALOG NUMBER: HC6R07D010-HM60525835-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P583332

CATALOG NUMBER: HC6R07D010-HM60525835-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	91	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70			
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61			
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57			
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			
10	72	62	56	52	71	61	56	52	60	55	52	60	55	52	59	55	51	50			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46937
5°	47964
10°	50840
15°	56828
20°	59499
25°	49612
30°	34721
35°	23383
40°	12044
45°	4179
50°	1868
55°	621
60°	285
65°	246
70°	192
75°	148
80°	221
85°	0



TEST NUMBER: P583332

CATALOG NUMBER: HC6R07D010-HM60525835-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.5	8.3
10°-20°	282.1	27.9
20°-30°	366.7	36.2
30°-40°	216.6	21.4
40°-50°	51.7	5.1
50°-60°	7.6	0.8
60°-70°	1.9	0.2
70°-80°	0.8	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	733.3	72.5
0°-40°	949.9	93.9
0°-60°	1009.2	99.7
0°-90°	1011.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1011.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	872	84
15°	1001	282
25°	820	367
35°	349	217
45°	54	52
55°	6	8
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583332

CATALOG NUMBER: HC6R07D010-HM60525835-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	856.2
2.5°	858.1
5°	871.6
7.5°	889.0
10°	913.3
12.5°	951.8
15°	1001.3
17.5°	1034.7
20°	1019.9
22.5°	945.5
25°	820.2
27.5°	677.0
30°	548.5
32.5°	443.8
35°	349.4
37.5°	257.0
40°	168.3
42.5°	91.9
45°	53.9
47.5°	33.4
50°	21.9
52.5°	12.8
55°	6.5
57.5°	3.2
60°	2.6
62.5°	2.6
65°	1.9
67.5°	1.2
70°	1.2
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)