

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583371

Luminaire Tested: **HC607D010-HM60525930-61MDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583371
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525930-61MDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 748.1 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.03
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583371

CATALOG NUMBER: HC607D010-HM60525930-61MDW

Luminous Intensity Polar Plot





TEST NUMBER: P583371

CATALOG NUMBER: HC607D010-HM60525930-61MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27849
5°	27746
10°	27282
15°	26799
20°	25879
25°	24534
30°	22320
35°	17835
40°	11894
45°	8482
50°	7062
55°	6165
60°	5811
65°	5487
70°	5033
75°	4702
80°	4262
85°	3774



TEST NUMBER: P583371

CATALOG NUMBER: HC607D010-HM60525930-61MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.7	6.4
10°-20°	132.6	17.7
20°-30°	185.3	24.8
30°-40°	163.2	21.8
40°-50°	88.2	11.8
50°-60°	59.0	7.9
60°-70°	41.8	5.6
70°-80°	23.5	3.1
80°-90°	6.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.6	48.9
0°-40°	528.8	70.7
0°-60°	675.9	90.4
0°-90°	748.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	748.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	508	
5°	504	48
15°	472	133
25°	406	185
35°	266	163
45°	109	88
55°	64	59
65°	42	42
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P583371

CATALOG NUMBER: HC607D010-HM60525930-61MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	508.0
2.5°	505.3
5°	504.2
7.5°	499.3
10°	490.1
12.5°	481.4
15°	472.2
17.5°	459.8
20°	443.6
22.5°	425.7
25°	405.6
27.5°	382.4
30°	352.6
32.5°	315.8
35°	266.5
37.5°	212.8
40°	166.2
42.5°	131.1
45°	109.4
47.5°	94.7
50°	82.8
52.5°	73.1
55°	64.5
57.5°	58.5
60°	53.0
62.5°	47.7
65°	42.3
67.5°	36.8
70°	31.4
72.5°	26.5
75°	22.2
77.5°	17.9
80°	13.5
82.5°	9.7
85°	6.0
87.5°	2.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)