

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584101

Luminaire Tested: **HC825D010-HM82555827-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555827-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2445.5 lumens
Efficiency: N/A
Efficacy: 91.3 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584101

CATALOG NUMBER: HC825D010-HM82555827-81MDW

Luminous Intensity Polar Plot





TEST NUMBER: P584101

CATALOG NUMBER: HC825D010-HM82555827-81MDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90	90	90	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80	80	80	80
3	98	89	83	78	95	88	82	78	85	80	76	83	78	75	80	77	74	72	72	72	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65	65	65	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59	59	59	59
6	81	70	63	58	79	69	62	57	67	61	57	66	61	56	64	60	56	54	54	54	54
7	76	65	58	53	74	64	57	53	63	57	52	62	56	52	60	55	52	50	50	50	50
8	72	61	54	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	43	43	43
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40	40	40	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62533
5°	60831
10°	57241
15°	54198
20°	52130
25°	50121
30°	44512
35°	28350
40°	15820
45°	13253
50°	11960
55°	11274
60°	10287
65°	9274
70°	8186
75°	7280
80°	6464
85°	5838



TEST NUMBER: P584101

CATALOG NUMBER: HC825D010-HM82555827-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.2	7.5
10°-20°	478.8	19.6
20°-30°	667.9	27.3
30°-40°	480.6	19.7
40°-50°	238.2	9.7
50°-60°	186.3	7.6
60°-70°	126.1	5.2
70°-80°	65.5	2.7
80°-90°	18.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1329.9	54.4
0°-40°	1810.5	74.0
0°-60°	2235.0	91.4
0°-90°	2445.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2445.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2028	
5°	1965	183
15°	1698	479
25°	1473	668
35°	753	481
45°	304	238
55°	210	186
65°	127	126
75°	61	66
85°	16	19
90°	0	



TEST NUMBER: P584101

CATALOG NUMBER: HC825D010-HM82555827-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2027.9
2.5°	2009.8
5°	1965.2
7.5°	1902.4
10°	1828.1
12.5°	1758.8
15°	1697.7
17.5°	1639.9
20°	1588.6
22.5°	1537.5
25°	1473.1
27.5°	1380.5
30°	1250.1
32.5°	1045.3
35°	753.1
37.5°	513.6
40°	393.0
42.5°	338.5
45°	303.9
47.5°	274.1
50°	249.3
52.5°	227.9
55°	209.7
57.5°	188.2
60°	166.8
62.5°	145.3
65°	127.1
67.5°	109.0
70°	90.8
72.5°	76.0
75°	61.1
77.5°	47.9
80°	36.4
82.5°	26.4
85°	16.5
87.5°	8.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)