

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584128

Luminaire Tested: **HC825D010-HM82555830-81WDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555830-81WDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2476.8 lumens
Efficiency: N/A
Efficacy: 92.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584128

CATALOG NUMBER: HC825D010-HM82555830-81WDW

Luminous Intensity Polar Plot





TEST NUMBER: P584128

CATALOG NUMBER: HC825D010-HM82555830-81WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89			89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79			79
3	97	88	82	76	94	87	81	76	84	79	75	81	77	73	79	75	72	70			70
4	90	80	73	68	88	79	73	67	77	71	67	75	70	66	73	68	65	63			63
5	84	74	66	61	82	73	66	61	71	65	60	69	64	59	67	63	59	57			57
6	79	68	61	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52			52
7	74	63	56	50	73	62	55	50	61	54	50	59	54	50	58	53	49	48			48
8	70	58	51	46	69	58	51	46	57	50	46	55	50	46	54	49	45	44			44
9	66	54	47	43	65	54	47	42	53	47	42	52	46	42	51	46	42	40			40
10	62	51	44	39	61	50	44	39	49	43	39	49	43	39	48	43	39	37			37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	49520
5°	49455
10°	48969
15°	48381
20°	47933
25°	47396
30°	44722
35°	36417
40°	20119
45°	13427
50°	11907
55°	11182
60°	11039
65°	10937
70°	9890
75°	8840
80°	7725
85°	6864



TEST NUMBER: P584128

CATALOG NUMBER: HC825D010-HM82555830-81WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.4	6.1
10°-20°	427.9	17.3
20°-30°	635.8	25.7
30°-40°	572.6	23.1
40°-50°	253.8	10.2
50°-60°	188.0	7.6
60°-70°	146.2	5.9
70°-80°	79.3	3.2
80°-90°	21.7	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1215.2	49.1
0°-40°	1787.8	72.2
0°-60°	2229.7	90.0
0°-90°	2476.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2476.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1606	
5°	1598	151
15°	1516	428
25°	1393	636
35°	967	573
45°	308	254
55°	208	188
65°	150	146
75°	74	79
85°	19	22
90°	0	



TEST NUMBER: P584128

CATALOG NUMBER: HC825D010-HM82555830-81WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1605.9
2.5°	1602.5
5°	1597.7
7.5°	1584.9
10°	1563.9
12.5°	1539.7
15°	1515.5
17.5°	1491.4
20°	1460.7
22.5°	1430.1
25°	1393.0
27.5°	1336.5
30°	1256.0
32.5°	1139.9
35°	967.4
37.5°	722.2
40°	499.8
42.5°	369.3
45°	307.9
47.5°	272.4
50°	248.2
52.5°	225.7
55°	208.0
57.5°	193.5
60°	179.0
62.5°	166.1
65°	149.9
67.5°	130.5
70°	109.7
72.5°	91.9
75°	74.2
77.5°	58.0
80°	43.5
82.5°	30.6
85°	19.4
87.5°	8.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)