

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583706

Luminaire Tested: **HC810D010-HM80520827-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583706
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC810D010-HM80520827-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1238.9 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583706

CATALOG NUMBER: HC810D010-HM80520827-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P583706

CATALOG NUMBER: HC810D010-HM80520827-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28366
5°	27726
10°	26875
15°	26331
20°	26095
25°	25709
30°	24348
35°	20230
40°	11911
45°	7880
50°	6203
55°	4564
60°	3170
65°	1926
70°	847
75°	369
80°	284
85°	0



TEST NUMBER: P583706

CATALOG NUMBER: HC810D010-HM80520827-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.3	6.8
10°-20°	233.2	18.8
20°-30°	345.5	27.9
30°-40°	319.2	25.8
40°-50°	147.2	11.9
50°-60°	77.4	6.2
60°-70°	27.3	2.2
70°-80°	4.3	0.3
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.0	53.5
0°-40°	982.2	79.3
0°-60°	1206.9	97.4
0°-90°	1238.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1238.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	896	84
15°	825	233
25°	756	345
35°	537	319
45°	181	147
55°	85	77
65°	26	27
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P583706

CATALOG NUMBER: HC810D010-HM80520827-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	919.9
2.5°	912.1
5°	895.7
7.5°	877.8
10°	858.3
12.5°	839.6
15°	824.8
17.5°	811.6
20°	795.2
22.5°	777.3
25°	755.6
27.5°	725.9
30°	683.8
32.5°	623.8
35°	537.4
37.5°	412.8
40°	295.9
42.5°	222.0
45°	180.7
47.5°	153.5
50°	129.3
52.5°	105.9
55°	84.9
57.5°	67.0
60°	51.4
62.5°	38.9
65°	26.4
67.5°	15.6
70°	9.4
72.5°	5.4
75°	3.1
77.5°	2.3
80°	1.6
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)