

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593621

Luminaire Tested: **HC825D010-HM82555850-81NDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555850-81NDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2506.5 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.57
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593621

CATALOG NUMBER: HC825D010-HM82555850-81NDH

Luminous Intensity Polar Plot





TEST NUMBER: P593621

CATALOG NUMBER: HC825D010-HM82555850-81NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 100 | 99 | 98 | 97 | 96 | 95 | 95 | 95 | 95 |
| 2 | 109 | 105 | 101 | 98 | 107 | 103 | 100 | 97 | 100 | 97 | 95 | 97 | 95 | 93 | 94 | 92 | 91 | 89 | 89 | 89 | 89 |
| 3 | 104 | 99 | 94 | 91 | 102 | 97 | 93 | 90 | 95 | 91 | 88 | 92 | 90 | 87 | 90 | 88 | 86 | 84 | 84 | 84 | 84 |
| 4 | 100 | 93 | 88 | 84 | 98 | 92 | 87 | 84 | 90 | 86 | 83 | 88 | 85 | 82 | 86 | 83 | 81 | 80 | 80 | 80 | 80 |
| 5 | 96 | 88 | 83 | 79 | 94 | 87 | 82 | 79 | 86 | 81 | 78 | 84 | 80 | 77 | 82 | 79 | 77 | 75 | 75 | 75 | 75 |
| 6 | 92 | 84 | 78 | 75 | 90 | 83 | 78 | 74 | 81 | 77 | 74 | 80 | 76 | 73 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 7 | 88 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 68 | 68 | 68 | 68 |
| 8 | 84 | 76 | 71 | 67 | 83 | 75 | 70 | 67 | 74 | 70 | 66 | 73 | 69 | 66 | 72 | 69 | 66 | 65 | 65 | 65 | 65 |
| 9 | 81 | 72 | 67 | 64 | 80 | 72 | 67 | 63 | 71 | 66 | 63 | 70 | 66 | 63 | 69 | 66 | 63 | 62 | 62 | 62 | 62 |
| 10 | 78 | 69 | 64 | 61 | 77 | 69 | 64 | 61 | 68 | 63 | 60 | 67 | 63 | 60 | 67 | 63 | 60 | 59 | 59 | 59 | 59 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 199449 |
| 5° | 168975 |
| 10° | 122602 |
| 15° | 92069 |
| 20° | 72643 |
| 25° | 58596 |
| 30° | 43422 |
| 35° | 17595 |
| 40° | 7423 |
| 45° | 3982 |
| 50° | 1785 |
| 55° | 903 |
| 60° | 574 |
| 65° | 409 |
| 70° | 334 |
| 75° | 214 |
| 80° | 320 |
| 85° | 637 |



TEST NUMBER: P593621

CATALOG NUMBER: HC825D010-HM82555850-81NDH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 468.7 | 18.7 |
| 10°-20° | 810.0 | 32.3 |
| 20°-30° | 783.2 | 31.2 |
| 30°-40° | 344.0 | 13.7 |
| 40°-50° | 74.4 | 3.0 |
| 50°-60° | 16.7 | 0.7 |
| 60°-70° | 5.7 | 0.2 |
| 70°-80° | 2.2 | 0.1 |
| 80°-90° | 1.7 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2061.9 | 82.3 |
| 0°-40° | 2405.8 | 96.0 |
| 0°-60° | 2496.9 | 99.6 |
| 0°-90° | 2506.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 2506.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 6468 | |
| 5° | 5459 | 469 |
| 15° | 2884 | 810 |
| 25° | 1722 | 783 |
| 35° | 467 | 344 |
| 45° | 91 | 74 |
| 55° | 17 | 17 |
| 65° | 6 | 6 |
| 75° | 2 | 2 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P593621

CATALOG NUMBER: HC825D010-HM82555850-81NDH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 6468.0 |
| 1° | 6419.7 |
| 2° | 6287.4 |
| 3° | 6049.1 |
| 4° | 5764.3 |
| 5° | 5458.9 |
| 6° | 5125.6 |
| 7° | 4790.5 |
| 8° | 4475.9 |
| 9° | 4183.6 |
| 10° | 3915.5 |
| 11° | 3662.3 |
| 12° | 3435.1 |
| 13° | 3228.4 |
| 14° | 3046.0 |
| 15° | 2884.0 |
| 17.5° | 2520.9 |
| 20° | 2213.7 |
| 22.5° | 1943.8 |
| 25° | 1722.2 |
| 27.5° | 1496.9 |
| 30° | 1219.5 |
| 32.5° | 828.5 |
| 35° | 467.4 |
| 37.5° | 275.5 |
| 40° | 184.4 |
| 42.5° | 130.3 |
| 45° | 91.3 |
| 47.5° | 59.6 |
| 50° | 37.2 |
| 52.5° | 22.4 |
| 55° | 16.8 |
| 57.5° | 13.1 |
| 60° | 9.3 |
| 62.5° | 7.5 |
| 65° | 5.6 |
| 67.5° | 3.7 |
| 70° | 3.7 |
| 72.5° | 1.8 |
| 75° | 1.8 |
| 77.5° | 1.8 |
| 80° | 1.8 |
| 82.5° | 1.8 |



TEST NUMBER: P593621

CATALOG NUMBER: HC825D010-HM82555850-81NDH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







| | | |
|-------|--|-----|
| 85° | | 1.8 |
| 87.5° | | 1.8 |



(END OF REPORT)