

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584178

Luminaire Tested: **HC825D010-HM82555927-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC825D010-HM82555927-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2118.3 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584178

CATALOG NUMBER: HC825D010-HM82555927-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P584178

CATALOG NUMBER: HC825D010-HM82555927-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			
4	93	84	78	73	91	83	77	72	81	76	72	79	74	71	77	73	70	68			
5	87	78	71	66	86	77	70	66	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	64	59	54	63	58	54	62	57	54	52			
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	53	47	43	53	47	43	52	46	43	51	46	42	41			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48496
5°	47403
10°	45950
15°	45023
20°	44616
25°	43949
30°	41631
35°	34587
40°	20368
45°	13471
50°	10607
55°	7806
60°	5415
65°	3305
70°	1434
75°	643
80°	479
85°	0



TEST NUMBER: P584178

CATALOG NUMBER: HC825D010-HM82555927-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	6.8
10°-20°	398.7	18.8
20°-30°	590.7	27.9
30°-40°	545.8	25.8
40°-50°	251.7	11.9
50°-60°	132.4	6.2
60°-70°	46.8	2.2
70°-80°	7.4	0.3
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1133.6	53.5
0°-40°	1679.4	79.3
0°-60°	2063.5	97.4
0°-90°	2118.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2118.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1573	
5°	1531	144
15°	1410	399
25°	1292	591
35°	919	546
45°	309	252
55°	145	132
65°	45	47
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P584178

CATALOG NUMBER: HC825D010-HM82555927-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1572.7
2.5°	1559.4
5°	1531.4
7.5°	1500.8
10°	1467.5
12.5°	1435.5
15°	1410.3
17.5°	1387.6
20°	1359.6
22.5°	1329.0
25°	1291.7
27.5°	1241.1
30°	1169.2
32.5°	1066.7
35°	918.8
37.5°	705.8
40°	506.0
42.5°	379.5
45°	308.9
47.5°	262.4
50°	221.1
52.5°	181.2
55°	145.2
57.5°	114.5
60°	87.8
62.5°	66.6
65°	45.3
67.5°	26.6
70°	15.9
72.5°	9.3
75°	5.4
77.5°	4.0
80°	2.7
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)